



Locking Devices, Marine Grade, Female Connector Body, 30A 125V, 2-Pole 3-Wire Grounding, L5-30R, Screw Terminal, Yellow, Corrosion Resistant

By Bryant
Catalog # [70530NCCR](#)



Locking Devices, Marine Grade, Female Connector Body, 30A 125V, 2-Pole 3-Wire Grounding, L5-30R, Screw Terminal, Yellow, Corrosion Resistant

Features

- Nickel-plated copper-alloy metallic components
- Molded of impact/chemical resistant high-visibility yellow nylon
- Stainless steel screws
- Triple Gripper® cord grip on plugs and connectors which feature three captive assembly screws to automatically tighten cord grip
- Individual wire pockets with clamp-type terminals

Application

Heavy Duty Industrial

General

Color	Yellow, White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	30A Triple Gripper Nylon Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786688780

Dimensions

Dimensions	2.13 in x 2.13 in x 3.90 in
Display Size	Standard Sized Product
Height	3.90 in
Length	2.13 in
Width	2.13 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current Rating	30 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Conductors	3-Wire Grounding
Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG

Certifications and Compliance

Nema Rating	L5-30R
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant J-3 Catalog page](#)
[Catalog Page - Bryant H-11 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[70530NPCR - Locking Devices, Marine Grade, Male Plug, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Yellow, Corrosion Resistant](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-70530NCCR-SPEC-EN | REV 5/2023

