



Locking Devices, Industrial, Male Plug, 30A 3- Phase Delta 250V AC, 3-Pole 3-Wire Non-Grounding, L11-30P, Screw Terminal, Black and White

By Bryant
Catalog # [71130NP](#)



Locking Devices, Industrial, Male Plug, 30A 3-Phase Delta 250V AC, 3-Pole 3-Wire Non-Grounding, L11-30P, Screw Terminal, Black and White.

Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

Application

Extra Heavy Duty Industrial

General

Color	Black, White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Triple Gripper Nylon Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Type	Plugs
UPC	781786693821

Dimensions

Dimensions	2.13 in x 2.13 in x 2.86 in
Display Size	Standard Sized
Height	2.86 in
Length	2.13 in
Width	2.13 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current Rating	30 A
Phase	Three Phase
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250 VAC

Conductor Related

Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG

Certifications and Compliance

Nema Rating	L11-30P
-------------	---------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant H-12 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [BLD - Straight Blade Devices, Plugbox Devices, Accessories, Red polypropylene Medium Lockout Device, Red](#)
- [71130ER - Locking Devices, Industrial, Flanged Receptacle, 30A 3-Phase Delta 250V AC, 3-Pole 3-Wire Non Grounding, L11-30R, Screw Terminal, White](#)
- [71130FR - Locking Devices, Industrial, Flush Receptacle, 30A 3-Phase Delta 250V AC, 3-Pole 3-Wire Non-Grounding, L11-30R, Screw Terminal, Black](#)
- [71130NC - Locking Devices, Industrial, Female Connector Body, 30A 3-Phase Delta 250V AC, 3-Pole 3-Wire Non-Grounding, L11-30R, Screw Terminal, Black and White](#)
- [72002BP - Locking Devices, Accessories, Short Weatherproofing Boot, For 20A and 30A, Yellow](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-71130NP-SPEC-EN | REV 5/2023