



# Locking Devices, Bryant Midget Locking, Industrial, Female Connector Body, 15A 125/250V, 3-Pole 3-Wire Non Grounding, ML-3R, Screw Terminal & White

By Bryant  
Catalog # [7484NC](#)



Locking Devices, Bryant Midget Locking, Industrial, Female Connector Body, 15A 125/250V, 3-Pole 3-Wire Non Grounding, ML-3R, Screw Terminal, Black & White

## Features

- Smaller body size for use in tighter fit applications where larger products can't
- Abuse resistant nylon housing

## Application

Heavy Duty Industrial

## General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Midget Female Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Non-Grounding
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786669352

## Dimensions

Dimensions	1.25 in x 1.25 in x 2.15 in
Display Size	Midget NEMA Locking
Height	2.15 in
Length	1.25 in
Width	1.25 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current Rating	15 A
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V

## Conductor Related

Conductor Range	#14 AWG
Number Of Conductors	3-Wire Non-Grounding
Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

## Certifications and Compliance

Nema Rating	ML-3R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant H-4 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

[7485NP - Locking Devices, Bryant Midget Locking, Industrial, Male Plug, 15A 125/250V, 3-Pole 3-Wire Non Grounding, ML-3P, Screw Terminal, Black](#)

[7486MB - Locking Devices, Bryant Midget Locking, Industrial, Flanged Inlet, 15A 125/250V, 3-Pole 3-Wire Non Grounding, ML-3P, Screw Terminal, Black & White](#)

[7400BCR - Straight Blade Devices, Locking Devices, Accessories, Weatherproof Boot for Midget Devices, For 15A, 2-Pole 2-Wire, Yellow](#)

[7487ER - Locking Devices, Bryant Midget Locking, Industrial, Receptacle, 15A 125/250V, 3-Pole 3-Wire Non Grounding, ML-3R, Screw Terminal, Black & White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-7484NC-SPEC-EN | REV 7/2023