



# Locking Devices, Industrial, Female Connector Body, 30A 3-Phase Delta 480V AC, 3-Pole 3-Wire Non-Grounding, L12-30R, Screw Terminal, Black and White

By Bryant  
Catalog # [71230NC](#)



Locking Devices, Industrial, Female Connector Body, 30A 3-Phase Delta 480V AC, 3-Pole 3-Wire Non-Grounding, L12-30R, Screw Terminal, Black and White

## Features

- Face and body feature alignment keys for easy assembly
- Amperage, voltage and NEMA configuration imprinted on face for easy identification
- Impact/chemical resistant, toughened nylon construction
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

## Application

Heavy Duty Industrial

## General

Color	Black, White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	30A Triple Gripper Nylon Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786694392

## Dimensions

Dimensions	2.13 in x 2.13 in x 3.90 in
Display Size	Standard Sized Product
Height	3.90 in
Length	2.13 in
Width	2.13 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current Rating	30 A
Voltage Rating	3 Phase 480 VAC
Voltage Rating Description	3 Phase 480 VAC

## Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Conductors	3-Wire Non-Grounding
Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG

## Certifications and Compliance

Nema Rating	L12-30R
-------------	---------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant H-12 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

- [71230MB - Locking Devices, Industrial, Flanged Inlet, 30A 3-Phase Delta 480V AC, 3-Pole 3-Wire Non-Grounding, L12-30P, Screw Terminal, White](#)
- [71230NP - Locking Devices, Industrial, Male Plug, 30A 3-Phase Delta 480V AC, 3-Pole 3-Wire Non-Grounding, L12-30P, Screw Terminal, Black and White](#)
- [70204ANA - Locking Devices, Accessories, Angle Adapter for Plugs and Connectors, For 20A and 30A Black and White](#)
- [72002BCB - Locking Devices, Accessories, Long Weatherproofing Boot, For 20A and 30A, Black](#)
- [72002BC - Locking Devices, Accessories, Long Weatherproofing Boot, For 20A and 30A, Yellow](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-71230NC-SPEC-EN | REV 5/2023