



Locking Devices, Industrial, Flanged Receptacle, 30A 3-Phase Wye 120/208V AC, 4-Pole 4-Wire Non-Grounding, L18-30R, Screw Terminal, White

By Bryant
Catalog # [71830ER](#)



Locking Devices, Industrial, Flanged Receptacle, 30A 3-Phase
Wye 120/208V AC, 4-Pole 4-Wire Non-Grounding, L18-30R,
Screw Terminal, White

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

Application

Extra Heavy Duty Industrial Specification Grade

General

| | |
|------------------------------|----------------------------------------------------|
| Color | White |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Item Type | 30A Flanged Receptacle |
| Material | Composite |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 4-Pole |
| OEM Brand Name | Hubbell Bryant |
| Style | Equipment Base |
| Type | Flanged Receptacle |
| UPC | 781786698406 |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 2.88 in x 2.88 in x 2.02 in |
| Display Size | Standard Sized Product |
| Height | 2.02 in |
| Length | 2.88 in |
| Width | 2.88 in |

Electrical Ratings

| | |
|----------------------------|-----------------------|
| Amperage Rating | 30 A |
| Connectivity | Terminal Screws |
| Current Rating | 30 A |
| Phase | Three Phase |
| Voltage Rating | 3 Phase Y 120/208 VAC |
| Voltage Rating Description | 3 Phase Y 120/208V AC |

Conductor Related

| | |
|-----------------|-------------------|
| Number Of Wires | 4-Wire |
| Wire Size | #14 AWG to #8 AWG |

Certifications and Compliance

| | |
|-------------|---------|
| Nema Rating | L18-20R |
|-------------|---------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalog Page - Bryant Q-19 Catalog page](#)
[Catalog Page - Bryant H-13 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[71830NP - Locking Devices, Industrial, Male Plug, 30A 3-Phase Wye 120/208V AC, 4-Pole 4-Wire Non-Grounding, L18-30P, Screw Terminal, Black and White](#)
[WPC2 - Wallplates and Boxes, Weatherproof Covers, 1-Gang, For Large Flanged Devices, Standard Size, Reinforced thermoplastic polyester](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-71830ER-SPEC-EN | REV 5/2023