



# Locking Devices, Elastomeric, Male Plug, 30A 3- Phase 600V AC, 3-Pole 4-Wire Grounding, L17-30P, Screw Terminal, Yellow, Water/Dust-Tight Housing

By Bryant  
Catalog # [BRY28W77](#)



Watertight Devices, Locking Devices, Elastomeric, Male Plug, 30A 3-Phase 600V AC, 3-Pole 3-Wire Non-Grounding, L17-30P, Screw Terminal, Yellow, Water/Dust-Tight Housing

## Features

- Triple bypass seal keeps water away from electrical connections and works with previously installed devices
- Corrosion-resistant connection points
- High conductivity brass termination
- Cone seal accomodates any cable range
- Keyed interior for easy installation

## General

Color	Yellow
Item Type	30A Watertight Plug
Number Of Poles	3-Pole
Performance	<ul style="list-style-type: none"> <li>• Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V</li> <li>• Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12</li> <li>• UV resistance:All exposed materials are UV stabilized</li> <li>• Flammability:UL94V2 (plugs, connectors, and interiors)</li> </ul>
Type	Plugs
UPC	781786378810

## Dimensions

Dimensions	2.77 in x 2.77 in x 3.94 in
Height	3.94 in
Length	2.77 in
Width	2.77 in

## Electrical Ratings

Amperage Rating	30 A
Voltage Rating	3 Phase 600 VAC
Voltage Rating Description	3 Phase 600 VAC

## Conductor Related

Number Of Wires	3-Wire
Wire Size	Min. cords: #12/3 SJ, #16/3 S, #14/4 SJ, #18/4 S, #18/5 S;Max. cord: #8/3 S, #8/4 S, #10/5 S

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• IP69K</li> <li>• Listed to UL498</li> <li>• Certified to CSA C22.2 No. 42</li> <li>• Meets NEMA® WD-1, WD-6, and ANSI Standards</li> <li>• IP66 Suitability</li> <li>• NSF Certified (plugs, connectors and receptacles)</li> </ul>
Nema Rating	L17-30P

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant I-7 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Watertight Wiring Devices](#)

## Related Products

[BRY29W77 - Locking Devices, Elastomeric, Female Connector Body, 30A 3-Phase Delta 600V AC, 3-Pole 4-Wire Grounding, L17-30R, Water/Dust-Tight Housing](#)  
[BRYWTCS3 - Watertight Replacement Cone Seal, Size 3](#)  
[BRYWTB3 - Watertight Replacement Bushing Set, Size 3](#)  
[BRY69W77 - Watertight Series, Locking Receptacle, 30A 3-Phase 600 AC, 3-Pole 4-Wire Grounding, NEMA L17-30R, Yellow](#)





A proud member of the Hubbell Family.