



Straight Blade Devices, Receptacles, Duplex, Decorator Hospital Grade, Isolated Ground, Back and Side Wired, 15A 125V, 2- Pole 3-Wire Grounding, 5-15R

By Bryant
Catalog # [9200IGRED](#)



Straight Blade Devices, Receptacles, Duplex, Decorator
Hospital Grade, Isolated Ground, Back and Side Wired, 15A
125V, 2-Pole 3-Wire Grounding, 5-15R, Red, Single Pack

Application

Hospital Grade

General

| | |
|------------------------------|--|
| Color | Red |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Item Type | Decorator Duplex |
| Material | Composite |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| OEM Brand Name | Hubbell Bryant |
| Series | Straight Blade |
| Style | Decorator |
| Type | Single Receptacle |
| UPC | 781786741690 |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 3.28 in x 1.36 in x 1.03 in |
| Display Size | Standard Sized Product |
| Height | 1.03 in |
| Length | 3.28 in |
| Weight | 0.25 lb |
| Width | 1.36 in |

Electrical Ratings

| | |
|----------------------------|---------------------|
| Amperage Rating | 15 A |
| Connectivity | Back and Side Wired |
| Current / Amperage Rating | 15 A |
| Current Rating | 15 A |
| Phase | Single Phase |
| Voltage Rating | 125 V |
| Voltage Rating Description | 125 V |
| Wattage | 1875 |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire |
| Wire Size | #14 AWG to #12 AWG |

Certifications and Compliance

| | |
|-------------|-------|
| Nema Rating | 5-15R |
|-------------|-------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalog Page - Bryant B-3 Catalog page](#)
[Catalog Page - Bryant D-6 Catalog page](#)
[Catalog Page - Bryant A-4 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Installation Manuals - WIRING_PD2504_INSTALLINST](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-9200IGRED-SPEC-EN | REV 7/2023