



Locking Devices, Elastomeric, Male Plug, 15A 250V, 2-Pole 3-Wire Grounding, L6-15P, Screw Terminal, Yellow, Water/Dust-Tight Housing

By Bryant
Catalog # [BRY24W49](#)



Watertight Devices, Locking Devices, Elastomeric, Male Plug, 15A 250V, 2-Pole 3-Wire Grounding, L6-15P, Screw Terminal, Yellow, Water/Dust-Tight Housing

Features

- Triple bypass seal keeps water away from electrical connections and works with previously installed devices
- Corrosion-resistant connection points
- High conductivity brass termination
- Cone seal accomodates any cable range
- Keyed interior for easy installation

General

Color	Yellow
Item Type	15A Watertight Plug
Number Of Poles	2-Pole
Performance	<ul style="list-style-type: none"> • Dielectric voltage:2000V AC if rated 300V or less, 3000V AC if rated above 300V • Moisture resistance:UL Listed to 3R, 3RX, 4, 4X, 6, 6P, 12 • UV resistance:All exposed materials are UV stabilized • Flammability:UL94V2 (plugs, connectors, and interiors)
Type	Plugs
UPC	781786378308

Dimensions

Dimensions	1.85 in x 1.85 in x 3.21 in
Height	3.21 in
Length	1.85 in
Width	1.85 in

Electrical Ratings

Amperage Rating	15 A
Voltage Rating	250 V
Voltage Rating Description	250 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#16/3 SJ to #10/3 SJ, #18/3 S to #12/3 S

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • IP69K • Listed to UL498 • Certified to CSA C22.2 No. 42 • Meets NEMA® WD-1, WD-6, and ANSI Standards • IP66 Suitability • NSF Certified (plugs, connectors and receptacles)
----------------------	--

Nema Rating	L6-15P
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant I-5 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Watertight Wiring Devices](#)

Related Products

[BRY25W49 - Locking Devices, Elastomeric, Female Connector Body, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal, Yellow, Water/Dust-Tight Housing](#)
[BRY65W49D - Locking Devices, Watertight Series, Receptacle, Duplex, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Yellow](#)
[BRY65W49 - Watertight Series, Locking Receptacle, 15A 250VAC, 2-Pole 3-Wire Grounding, NEMA L6-15R, Yellow](#)
[BRYWTCS1 - Watertight Replacement Cone Seal, Size 1](#)
[BRYWTB1 - Watertight Replacement Bushing Set, Size 1](#)



