



Straight Blade Devices, Receptacles, Duplex, Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray, Single Pack

By Bryant
Catalog # [CRS15GRY](#)

Straight Blade Devices, Receptacles, Duplex, Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray, Single Pack



General

| | |
|------------------------------|---|
| Application | Commercial Specification Grade |
| Catalog Number | CRS15GRY |
| Color | Gray |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Item Type | Traditional Duplex Smooth Face |
| Material | Composite |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| OEM Brand Name | Hubbell Bryant |
| Series | Commercial |
| Style | Smooth Face |
| Type | Duplex Receptacle |
| UPC | 781786161016 |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 3.28 in x 1.38 in x 1.07 in |
| Display Size | Standard Sized Product |
| Height | 1.07 in |
| Length | 3.28 in |
| Weight | 0.2 lb |
| Width | 1.38 in |

Electrical Ratings

| | |
|----------------------------|-----------------|
| Amperage Rating | 15 A |
| Connectivity | Side Wired Only |
| Current / Amperage Rating | 15 A |
| Current Rating | 15 A |
| Phase | Single Phase |
| Voltage Rating | 125 V |
| Voltage Rating Description | 125 V |
| Wattage | 1875 |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire |
| Wire Size | #14 AWG to #12 AWG |

Certifications And Compliance

| | |
|------------------------------------|-------|
| Nema Rating | 5-15R |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------|------|
| Carton Quantity | 10 |
| Pallet Quantity | 9000 |

Product Assets

- [Catalog Page - BRY A-12 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Commercial Grade Receptacles and Switches](#)
- [Literature - General Literature - BRYANT® Wiring Devices](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-CRS15GRY-SPEC-EN | REV 6/2024