




# Locking Devices, Industrial, Receptacle, 50A 125/250, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black

By Bryant  
Catalog # [CS6369A](#)

Locking Devices, Industrial, Receptacle, 50A 125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black



## Features

- Thermoset construction offers high heat resistance
- Armored housing provides superior impact resistance
- One piece contacts provide low operating temperatures

## Application

Extra Heavy Duty Industrial Specification Grade

## General

Color	<ul style="list-style-type: none"><li>• Black</li><li>• Noir</li></ul>
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	50A Single Armored Nylon Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Type	<ul style="list-style-type: none"><li>• Receptacle</li><li>• Receptacle</li></ul>
UPC	781786253094

## Dimensions

Dimensions	3.28 in x 2.12 in x 2.44 in
Display Size	Standard Sized Product
Height	2.44 in
Length	3.28 in
Width	2.12 in

## Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current Rating	50 A
Phase	Single Phase
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250V AC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#10 AWG to #4 AWG

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant H-21 Catalog page](#)  
[Catalog Page - Bryant Q-18 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

[CS6365 - Locking Devices, Industrial, Male Plug, 50A 125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black and White](#)  
[SS750 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) 50A Twist-Lock® Opening, Standard Size, Stainless Steel](#)  
[7774CR - Wallplates and Boxes, Weatherproof Covers, 1- Gang, 1\) 50A Locking Opening, Standard Size, Yellow Polycarbonate](#)  
[7383 - Wallplates and Boxes, Weatherproof Covers, 1- Gang, 1\) 50A Locking Opening, Standard Size, Cast Aluminum](#)  
[7382 - Wallplates and Boxes, Non-Weatherproof Covers, 1- Gang, 1\) 50A Locking Opening, Standard Size, Cast Aluminum, Less Flip Lid](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-CS6369A-SPEC-EN | REV 7/2023