



Locking Devices, Industrial, Receptacle, 50A 125V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black

By Bryant
Catalog # [CS6370A](#)

Locking Devices, Industrial, Receptacle, 50A 125V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black



Features

- Thermoset construction offers high heat resistance
- Armored housing provides superior impact resistance
- One piece contacts provide low operating temperatures

Application

Extra Heavy Duty Industrial Specification Grade

General

Color	Black
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	50A Single Armored Heavy Duty Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Type	Receptacle
UPC	781786253100

Dimensions

Dimensions	3.28 in x 2.12 in x 2.44 in
Display Size	Standard Sized Product
Height	2.44 in
Length	3.28 in
Width	2.12 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current Rating	50 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125V AC

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant H-21 Catalog page](#)
[Catalog Page - Bryant Q-18 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[7382 - Wallplates and Boxes, Non-Weatherproof Covers, 1-Gang, 1\) 50A Locking Opening, Standard Size, Cast Aluminum, Less Flip Lid](#)
[7383 - Wallplates and Boxes, Weatherproof Covers, 1-Gang, 1\) 50A Locking Opening, Standard Size, Cast Aluminum](#)
[CS6361 - Locking Devices, Industrial, Male Plug, 50A 125V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black and White](#)
[SS750 - Wallplates and Boxes, Metallic Plates, 1-Gang, 1\) 50A Twist-Lock® Opening, Standard Size, Stainless Steel](#)
[7774CR - Wallplates and Boxes, Weatherproof Covers, 1-Gang, 1\) 50A Locking Opening, Standard Size, Yellow Polycarbonate](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-CS6370A-SPEC-EN | REV 7/2023