



# Watertight Series, Locking Receptacle, 15A 250VAC, 2-Pole 3-Wire Grounding, NEMA L6-15R, Yellow

By Bryant  
Catalog # [BRY65W49](#)



Watertight Series, Locking Receptacle, 15A 250V AC, 2-Pole 3-Wire Grounding, NEMA L6-15R, Yellow

## Features

- Impact-resistant PBT material lid and cover plate
- Stainless steel mounting hardware
- Lockable cover meets OSHA Lockout/Tagout regulations
- Thermoplasticelastomer seal

## General

Color	Yellow
Item Type	15A Watertight Single Receptacle
Number Of Poles	2-Pole
Performance	<ul style="list-style-type: none"> <li>• Moisture resistance: UL Listed to 3R, 3RX, 4, 4X, wet and damp locations (portable outlet boxes)</li> <li>• UV resistance: All exposed materials are UV stabilized</li> <li>• Flammability: UL94V0 (boxes, covers, and plates)</li> </ul>
Type	Receptacle
UPC	781786379190

## Dimensions

Dimensions	4.56 in x 3.10 in x 2.83 in
Height	2.83 in
Length	4.56 in
Width	3.10 in

## Electrical Ratings

Amperage Rating	15 A
Voltage Rating	250 V
Voltage Rating Description	250 V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• IP69K in use</li> <li>• Listed to UL498</li> <li>• Certified to CSA C22.2 No. 42</li> <li>• Meets NEMA® WD-1, WD-6, and ANSI Standards</li> <li>• IP66 Suitability</li> <li>• NSF Certified (plugs, connectors and receptacles)</li> </ul>
----------------------	---

Nema Rating	L6-15R
-------------	--------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant I-5 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - General Literature - Watertight Wiring Devices](#)

## Related Products

[BRY24W49 - Locking Devices, Elastomeric, Male Plug, 15A 250V, 2-Pole 3-Wire Grounding, L6-15P, Screw Terminal, Yellow, Water/Dust-Tight Housing](#)  
[BRY60CM88 - Weatherproof Boxes, 1-Gang, Blank Plate, FS/FD Style, Yellow](#)  
[BRY60CM88W - Watertight Series, 1-Gang, Blank Plate, White](#)  
[BRY60CM84AK - Watertight Series, Adapter Kit, 1" NPT, Yellow](#)  
[BRY60CM83WA - Watertight Series, FD Box, 3/4" NPT, White](#)



