



Locking Devices, Industrial, Male Plug, 50A 3- PhaseDelta 250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

By Bryant
Catalog # [CS8365](#)



Locking Devices, Industrial, Male Plug, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Heavy Duty Black

Features

- Super tough nylon housing offers better impact qualities
- Stainless steel shroud protects contacts and prevents mismatching
- Box terminal with hex socket threaded slug, permits high clamping pressure on conductors without damaging strands
- Thermoplastic polyester interior provides heat resistance and impact strength

Application

Extra Heavy Duty Industrial

General

| | |
|------------------------------|---|
| Color | Black |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Item Type | 50A Heavy Duty Male Plug |
| Material | Composite |
| Material - Mounting Hardware | Cord Mounted |
| Number Of Poles | 3-Pole |
| OEM Brand Name | Hubbell Bryant |
| Style | Extra Heavy Duty |
| Type | Plugs |
| UPC | 781786538177 |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 6.38 in x 2.56 in x 2.56 in |
| Display Size | Standard Sized |
| Height | 2.56 in |
| Length | 6.38 in |
| Width | 2.56 in |

Electrical Ratings

| | |
|----------------------------|-----------------|
| Amperage Rating | 50 A |
| Connectivity | Screw Terminals |
| Current Rating | 50 A |
| Phase | Three Phase |
| Voltage Rating | 3 Phase 250 VAC |
| Voltage Rating Description | 3 Phase 250 VAC |

Conductor Related

| | |
|-----------------|----------------------|
| Cord Type | All Listed Portables |
| Number Of Wires | 4-Wire |
| Wire Size | #18 AWG to #8 AWG |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalog Page - Bryant H-21 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[CS8369A - Locking Devices, Locking Devices, Industrial, Receptacle, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non- NEMA, Screw Terminal, Black](#)
[CS8364 - Locking Devices, Industrial, Female Connector Body, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black and White](#)
[7716B - Locking Devices, Accessories, Weatherproof Boot, Nylon Plug, For 50A Black](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-CS8365-SPEC-EN | REV 7/2023