

BRYANT®

**Timer Switches, Single Pole,
8.3A120/277V AC, 12 Hour Delay
Time Out, White**

By Bryant
Catalog # [DT5012W](#)

Timer Switches, Single Pole, 8.3A120/277V AC, 12 Hour Delay
Time Out, White



Features

- 12 hour timer
- Pre-set 5 button selection with permanent time markings
- Manual override to OFF
- Alert to OFF function - red LED will flash during the final 30 seconds
- Designed for use on 120 or 277V AC circuits

Performance

- Controls - 5 button selection - Preset time selection
- Controls - LED Indicators - Illuminates once time is selected
- Controls - OFF Switch - 6 seconds to 20 minutes (default set to 10 minutes)
- Electrical - Load Capacity - 120VAC 600W Incandescent, 5A Ballast, 5A CFL/LED 277V, Horsepower rating 1/6
- Environmental - Operating Temperature - 32°F to 122°F (0°C to 50°C) with rate of change not exceeding 20°F(11°C) per hour
- Environmental - Storage - -40°F to 150°F (-40°C to 65°C), 20% to 90% non condensing relative humidity

General

Catalog Number	DT5012W
Color	White
EU RoHS Indicator	No
Humidity	20% to 90% non-condensing relative humidity
Indicator	Illuminates once time is selected
Indicator(s) Type	Red LED
Item Type	Countdown Timer Wall Switch
Material	Polycarbonate
Operating Temperature	32°F to 122°F (0°C to 50°C) with rate of change not exceeding 20°F(11°C) per hour
Series	Fixed Countdown
Specifications	<ul style="list-style-type: none">• Housing - Polycarbonate• Mounting Bracket - Aluminum• Mounting Strap - Steel• Wire Leads - 6" 14AWG copper wire

Storage Temperature Range	-40°F to 150°F (-40°C to 65°C)
Timing Range	OFF, 2, 4,8, 12 hours
Type	12 Hours
UPC	783585256474

Dimensions

Dimensions	3.81 in x 1.75 in x 2.27 in
Height	2.27 in
Length	3.81 in
Width	1.75 in

Electrical Ratings

Connectivity	Wire Leads
Voltage Rating	120/277 VAC
Voltage Rating Description	120/277V AC
Wattage	1000/1400 W

Conductor Related

Wire Length	6 in
Wire Size	#14 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• cULus Listed To UL60730-1 And UL60730-2• Meets ASHRAE 90.1, and CEC Title 24 Compliant
----------------------	---

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK Z-20 Catalog Page](#)
[Catalog Page - WDK E-6 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - Multifamily Property Tech Enhancements](#)
[Literature - Residential Catalog](#)
[Literature - Property Management | Home Enhancements | Innovation and Convenience](#)
[Specifications - DT5012W](#)