



# Power Protection Products, Receptacles, GFCI, Commercial Grade, Self Test, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R, With Nightlight, Almond

By Bryant  
Catalog # [GFTRST20ALNL](#)



Power Protection Products, Receptacles, GFCI, Commercial  
Grade, Self Test, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R,  
With Nightlight, Almond

## Features

- Patented shutter design for tamper-resistant
- Compliant with NEC® 406.12 and NEC® 517-18(c)
- Patented AUTOGUARD® self test technology
- Triple wipe construction

## General

|                |                                                                                                                                                                                                                                                     |
|----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | GFTRST20ALNL                                                                                                                                                                                                                                        |
| Color          | Almond                                                                                                                                                                                                                                              |
| Series         | Heavy Duty                                                                                                                                                                                                                                          |
| Specifications | <ul style="list-style-type: none"><li>• Base - Nylon</li><li>• Face - Nylon</li><li>• Ground Contacts - Brass</li><li>• Mounting Screws - Zinc plated steel</li><li>• Mounting Strap - Zinc plated steel</li><li>• Power Contacts - Brass</li></ul> |
| Style          | Nightlight                                                                                                                                                                                                                                          |
| Type           | Tamper-Resistant                                                                                                                                                                                                                                    |
| UPC            | 883778123443                                                                                                                                                                                                                                        |

## Electrical Ratings

|                            |       |
|----------------------------|-------|
| Amperage Rating            | 20 A  |
| Current / Amperage Rating  | 20 A  |
| Voltage Rating Description | 125 V |

## Certifications And Compliance

|                      |                             |
|----------------------|-----------------------------|
| Industry Standard(s) | Meets All NEC® Requirements |
| Nema Rating          | 5-20R                       |

## Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

## Product Assets

- [Catalog Page - WDK Z-8 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - 2015 UL GFCI Requirements](#)
- [Literature - CIRCUITPRO® Self Test GFCI](#)
- [Sales Drawings - WDK\\_GFTRST20ALNL\\_DRAWINGS\\_PDF](#)
- [Specifications - GFTRST20ALNL](#)