



Combination Devices, Residential Grade, 1) Single Pole Toggle, 1) Pilot Light, 15A 120V AC, Self Grounding, Side Wired, Brown

By Bryant
Catalog # [RC109](#)

One Single-Pole Toggle One Pilot Light Combination Device,
Residential 15A 120V AC, Self Grounding, Side Wired



Features

- Quiet snap action mechanism
- Self-grounding staple is standard
- Elongated strap with continuous plaster ears

Application

Residential

General

Action	Snap Switch
Actuator	Toggle
Contact Configuration	Two Position
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Switch and Amber Pilot Light Combo Device
Material - Mounting Hardware	Mounting Screws
Number Of Poles	1) Single Pole
Operating Cycles	30,000 Minimum
Operating Temperature	Max Continuous- 60 Degrees C, Minimum- -20 Without Impact
Performance	Environmental - Operating temperature - -20°C to 60°C
UPC	883778110016

Dimensions

Display Size	Standard Size
--------------	---------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Contact Rating	15A
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	120 VAC
Voltage Rating Description	120 VAC
Wattage	1800

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant E-8 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[RC101 - Switches and Lighting Controls, Combination Devices, Residential Grade, 2\) Single Pole Toggles, 15A 120V AC, Self Grounding, Side Wired, Brown](#)

[RC109I - Combination Devices, Residential Grade, 1\) Single Pole Toggle, 1\) Pilot Light, 15A 120V AC, Self Grounding, Side Wired](#)

[RC109LA - Switches and Lighting Controls, Combination Devices, Residential Grade, 1\) Single Pole Toggle, 1\) Pilot Light, 15A 120V AC, Self Grounding, Side Wired](#)

[RC101W - Switches and Lighting Controls, Combination Devices, Residential Grade, 2\) Single Pole Toggles, 15A 120V AC, Self Grounding, Side Wired, White](#)

[RC108ALTR - Combination Devices, Residential Grade, 1\) Single Pole Toggle, 1\) Single Tamper Resistant Receptacle, 15A 120V AC, Self Grounding, Side Wired](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-RC109-SPEC-EN | REV 7/2023