



Combination Devices, Residential Grade, Decorator Series, 1) Single Pole Rocker, 1) Single Tamper Resistant Receptacle, 15A 120V AC, Side Wired

By Bryant
Catalog # [RCD108WTR](#)

Switches and Lighting Controls, Combination Devices,
Residential Grade, Decorator Series, 1) Single Pole Rocker, 1)
Single Tamper Resistant Receptacle, 15A 120V AC, Side Wired



General

Action	Snap Switch
Actuator	Rocker
Application	Residential
Catalog Number	RCD108WTR
Contact Configuration	Two Position
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Switch and Receptacle Combo Devices
Material - Mounting Hardware	Mounting Screws
Number Of Poles	1) Single Pole
Operating Cycles	30,000 Minimum
Operating Temperature	Max Continuous- 60 Degrees C, Minimum- -20 Without Impact
Performance	Electrical - Dielectric voltage - Withstands 1,500V AC minimum for 1 minute Electrical - Endurance - 30,000 cycles minimum Electrical - Max. working voltage - 120V Electrical - Overload - 1.5 times rating Environmental - Flammability - UL V0 Environmental - Operating temperatures - Maximum continuous 60°C minimum -20°C (without impact) Mechanical - Terminal accommodation - Back and side wire: #14 AWG min. - #12 AWG max. solid and stranded copper wire only push wire: #14 AWG solid copper wire only
UPC	883778302381

Dimensions

Display Size	Standard Size
--------------	---------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Contact Rating	15A
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	1875

Certifications And Compliance

Industry Standard(s)	CSA Certified UL Listed E3896
----------------------	----------------------------------

Logistics

Carton Quantity	10
Pallet Quantity	7200

Product Assets

[Catalog Page - WDK Z-4 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Catalogs - WDK Catalog Full 2024](#)
[Literature - Residential Catalog](#)
[Literature - General Literature - Tamper-Resistant and Weather Resistant Receptacles](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-RCD108WTR-SPEC-EN | REV 6/2024