



# Combination Devices, Residential Grade, 1) Three Way Toggle, 1) Single Receptacle, 15A 120V AC, Self Grounding, Side Wired

By Bryant  
Catalog # [RC308W](#)

One Three Way Toggle One Single Receptacle Combination Device, Residential 15A 120V AC, Self Grounding, Side Wired



## Features

- Quiet snap action mechanism
- Self-grounding staple is standard
- Elongated strap with continuous plaster ears

## Application

Residential

## General

Action	Snap Switch
Actuator	Toggle
Contact Configuration	Two Position
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Switch and Receptacle Combo Devices
Material - Mounting Hardware	Mounting Screws
Number Of Poles	1) Three Way
Operating Cycles	30,000 Minimum
Operating Temperature	Max Continuous- 60 Degrees C, Minimum- -20 Without Impact
Performance	Environmental - Operating temperature - -20°C to 60°C
UPC	883778109850

## Dimensions

Display Size	Standard Size
--------------	---------------

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Contact Rating	15A
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	120 VAC
Voltage Rating Description	120 VAC
Wattage	1800

## Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant E-7 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

- [RC309AL - COMBO, 15A 3W TOG, PILOT/ILLUM, AL](#)
- [RC303I - Switches and Lighting Controls, Combination Devices, Residential Grade, 2\) Three Way Toggles, 15A 120V AC, Self Grounding, Side Wired, Ivory](#)
- [RC103I - Combination Devices, Residential Grade, 1\) Single Pole Toggle, 1\) Three Way Toggle, 15A 120V AC, Self Grounding, Side Wired](#)
- [RC309I - Combination Devices, Residential Grade, 1\) Three Way Toggle, 1\) Pilot Light, 15A 120V AC, Self Grounding, Side Wired](#)
- [RC308 - Combination Devices, Residential Grade, 1\) Three Way Toggle, 1\) Single Receptacle, 15A 120V AC, Self Grounding, Side Wired, Brown](#)



A proud member of the Hubbell Family.