



# TradeSelect, Decorator Switch, Residential Grade, Rocker Switch, General Purpose AC, Illuminated Single Pole, 15A 120/277V AC, Push Back and Side

By Bryant  
Catalog # [RSD115ILI](#)



tradeSELECT® Decorator Switch, Residential Grade, Rocker Switch, General Purpose AC, Illuminated Single-Pole, 15A 120/277V AC, Push Back and Side

## Features

- Smooth, quiet rocker
- Self-grounding feature is standard
- Ultrasonically welded cover and base

## General

### Performance

- Electrical - Dielectric voltage - Withstands 1,500V AC minimum for 1 minute
- Electrical - Endurance - 30,000 cycles minimum
- Electrical - Max. working voltage - 120V
- Electrical - Overload - 1.5 times rating
- Environmental - Flammability - UL V0
- Environmental - Operating temperatures - Maximum continuous 60°C
- minimum -20°C (without impact)
- Mechanical - Terminal accommodation - Back and side wire: #14 AWG min. - #12 AWG max. solid and stranded copper wire only
- push wire: #14 AWG solid copper wire only

UPC

883778101175

## Certifications and Compliance

- |                      |                            |
|----------------------|----------------------------|
| Industry Standard(s) | • CSA Certified            |
|                      | • Listed to UL Standard 20 |

## Logistics

Carton Quantity 10

## Product Assets

[Catalog Page - Bryant E-6 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - Residential Catalog](#)

## Related Products

[RSD415I - TradeSelect, Decorator Switch, Residential Grade, Rocker Switch, General Purpose AC, 4 Way, 15A 120/277V AC, Push Back and Side Wired](#)  
[RSD115LAL - RESI ROCKER SW, SP, 15A 120V, ILL AL](#)  
[RSD115ILLA - TradeSelect, Decorator Switch, Residential Grade, Rocker Switch, General Purpose AC, Illuminated Single Pole, 15A 120/277V AC, Push Back and Side](#)  
[RSD115ILW - TradeSelect, Decorator Switch, Residential Grade, Rocker Switch, General Purpose AC, Illuminated Single Pole, 15A 120/277V AC, Push Back and Side](#)  
[RSD315ILI - TradeSelect, Decorator Switch, Residential Grade, Rocker Switch, General Purpose AC, Illuminated Three Way, 15A 120/277V AC, Push and Side Wired](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-RSD115ILI-SPEC-EN | REV 7/2023