



Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 20A 125V, 2-Pole 3- Wire Grounding, 5-20R

By Bryant
Catalog # [BRY5369NC](#)



Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 20A 125V, 2-Pole 3- Wire Grounding, 5-20R, Black, Single Pack

Features

- Heavy Duty
- Industrial/Commercial Grade
- Straight
- 20A 125V
- 2-Pole 3- Wire Grounding

Application

Extra Heavy Duty Industrial Grade

General

| | |
|------------------------------|---|
| Catalog Number | BRY5369NC |
| Color | Black and White |
| Cord Range | 0.300"-0.655" |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Insulation | Insulated Body |
| Item Type | Tech-Spec Triple Gripper |
| Material | Composite |
| Material - Mounting Hardware | Cord Mounted |
| Number Of Poles | 2-Pole |
| Series | Industrial |
| Style | Extra Heavy Duty |
| Temperature Rating | Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact. |
| Type | Plug |
| UPC | 781786005952 |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 2.95 in x 1.52 in x 1.38 in |
| Display Size | Standard Sized Product |
| Height | 1.38 in |
| Length | 2.95 in |
| Weight | 0.15 lb |
| Width | 1.52 in |

Electrical Ratings

| | |
|----------------------------|-----------------|
| Amperage Rating | 20 A |
| Connectivity | Screw Terminals |
| Current / Amperage Rating | 20 A |
| Current Rating | 20 A |
| Voltage Rating | 125 V |
| Voltage Rating Description | 125 V |

Conductor Related

| | |
|----------------------|--------------------|
| Conductor Range | #14 AWG to #10 AWG |
| Number Of Wires | 3-Wire |
| Number of Conductors | 3-Wire Grounding |

Certifications And Compliance

| | |
|-------------|-------|
| Nema Rating | 5-20P |
|-------------|-------|

Logistics

| | |
|-----------------|------|
| Carton Quantity | 10 |
| Pallet Quantity | 4500 |

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - BRY5369NC](#)