



TradeSelect, Straight Blade  
Devices, Residential Grade,  
Receptacles, Single, 30A 125/250V,  
3-Pole 4-Wire Grounding, 14-30R,  
Flush Mount, White

By Bryant  
Catalog # [RR430FW](#)

tradeSELECT® Straight Blade Residential Grade, Single, 30A  
125/250V, 3-Pole 4-Wire Grounding, Flush Mount

Features

- Sequenced contacts assure protection
- Catalog number, ratings and certifications molded in face
- One piece design power and ground contacts

Application

Residential Range and Dryer Devices

General

Color	<ul style="list-style-type: none"><li>• White</li><li>• Blanc</li></ul>
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Series	Heavy Duty
Style	Smooth Face
Type	Single Receptacle
UPC	883778100734

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V
Wattage	7500



Conductor Related

Number Of Wires	4-Wire
Wire Size	#10 AWG

Certifications and Compliance

Industry Standard(s)	UL Listed
Nema Rating	14-30R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant A-26 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Literature - Residential Catalog](#)

Related Products

[P703W - Wallplate, 2-Gang, 2.15" Opening, White](#)  
[RR450WIPCN - TradeSelect, Straight Blade, Single Panel Mount Receptacle, 50A 125/250V, 3-Pole 4-Wire Grounding, 14-50R, Black, With Plate](#)  
[RR430WIPCN - TradeSelect, Straight Blade, Single Panel Mount Receptacle, 30A 125/250V, 3-Pole 4-Wire Grounding, 14-30R, Black, With Plate](#)  
[RR430PM - TradeSelect, Straight Blade, Single Panel Mount Receptacle, 30A 125/250V, 3-Pole 4-Wire Grounding, 14-30R, Black](#)  
[RR450F - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 50A 125/250V, 3-Pole 4-Wire Grounding, 14-50R, Flush Mount, Black](#)



A proud member of the Hubbell Family.