



C22HD4/ODB

by Burndy
Catalog ID: C22HD4/ODB

Prop65

Cast Bronze ground Clamps, 3.60 in L, 1-1/4" - 2" Water Pipe (Run), #8 - 4/0 Ground (Tap).

Features: For Connecting Grounding Conductor, EMT Or Rigid Conduit To Water Pipe, Copper Tube, Ground Rod Or Rebar, Hub Swings 360° For Easy Alignment, Simply Reverse Bottom Clamp For Smaller Size Rebar Or Rod, Connectors Are Provided With Silicon Bronze Hardware, Length: 3.6 IN, Installation Torque: 50 IN-LB, Water Pipe Size: 1-1/4 - 2 IN, Width: 1.56 IN, Height: 2.7 IN

Product Details

General

Application	For Connecting Grounding Conductor, EMT Or Rigid Conduit To Water Pipe, Copper Tube, Ground Rod Or Rebar And Direct Burial
Installation Torque Recommended in-lb	50 LBS/in
Material	Bronze Alloy
Material - Hardware	Zinc Plated Steel
Plated	N
Plating Type	Zinc
Sub Brand	CLAMP
Type	WaterPipe Gounding Connectors
UPC	781810353196
UPC 12 Digit	7818103531966

Dimensions

Dimension - Height fraction	2.888888888888889 in
Dimension - Height inch	2.89 in
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.65 in
Dimension - Width inch	1.41 in
Dimension - Width mm	36 mm

Conductor Related

Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	8 AWG-4/0 AWG
Conductor - Pipe EMT Size	1 1/4 in;1 1/2 in;2 in
Conductor - Pipe EMT Size Range	1 1/4 -2

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)