

# NA18A4N

by Burndy  
Catalog ID: NA18A4N

Prop 65 Notice

Aluminium Bolted Terminal, Tube to Flat, 2" Al Pipe, 4 Pad Holes, 230 kV



## Product Details

### General

Application	Substation
Clamping Element Design	Body and Cap
Connector Type	Terminal
Installation Torque Recommended in-lb	480 LBS/in
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	3.12 x 3 - 4 holes
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
UPC	781810003763
UPC 12 Digit	7818100037633

### Dimensions

Dimension - B Length fraction	4-1/4 in
Dimension - B Length inch	4.25 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - G inch	2.05 in
Dimension - Height fraction	4-1/2
Dimension - Height inch	4.47 in
Dimension - Hole Size fraction	9/16
Dimension - L Length Overall mm	191 mm
Dimension - Length Overall inch	7.50 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	3.12 in
Dimension - Width fraction	4-1/2 in
Dimension - Width inch	4.50 in

Dimension - Width mm	114 mm
----------------------	--------

## Electrical Ratings

Rating - KVA	230 kV
--------------	--------

## Conductor Related

Conductor - AL Tube Std Size	2 IPS
Conductor - AL Tube Std Size Range	2 IPS
Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube Std Size	2 IPS IPS
Conductor - Copper Tube Std Size Range	2 IPS IPS
Conductor Type	<ul style="list-style-type: none"><li>• AL Tube Std-Size</li><li>• CU Tube Std-Size</li></ul>
Number Of Conductors	1

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)