



## UCT26RSC

by Burndy  
Catalog ID: UCT26RSC

Prop 65 Notice

Aluminum Parallel Groove Clamp with cover, Run: Cu & AL: 8 Sol. - 2/0,  
ACSR: 6 - 2/0, Tap: Cu & AL: 6 Sol. - 2/0, ACSR: 6 - 2/0

## Product Details

### General

Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	FASTAP™
UPC	781810643792
UPC 12 Digit	7818106437922

### Dimensions

Dimension - Height inch	2.62 in
Dimension - Length Overall inch	1.62 in
Dimension - Width inch	2.50 in

### Conductor Related

Conductor - AAAC 5005 Size	6 STR - 2/0 STR
Conductor - AAAC 5005 Size Range	6 STR - 2/0 STR
Conductor - AAAC 6201 Size	6 STR - 2/0 STR
Conductor - AAAC 6201 Size Range	6 STR - 2/0 STR
Conductor - ACSR Str Size	6 STR - 2/0 STR
Conductor - ACSR Str Size A Range	6 Str. - 2/0
Conductor - ACSR Str Size B Range	6 Str. - 2/0
Conductor - AL Str Size A	8 SOL - 2/0 STR
Conductor - AL Str Size A Range	8 Sol. 2/0
Conductor - AL Str Size B	8 SOL - 2/0 STR
Conductor - AL Str Size B Range	8 Sol. - 2/0 Str.
Conductor - Copper Solid Size	#8 - 2/0
Conductor - Copper Solid Size Range	#8 - 2/0
Conductor - Copper Str Size A Range	8 Sol. 2/0
Conductor - Copper Str Size B Range	8 Sol. - 2/0 Str.

Conductor Type

- AAAC C 5005-Size
- AAAC C 6201-Size
- ACSR C Str-Size
- AL C Str-Size A
- AL C Str-Size B
- CU C Solid-Size
- CU C Str-Size A
- CU C Str-Size B
- CU Weld C Solid-Size

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)