



# UCT26RS

by Burndy  
Catalog ID: UCT26RS

Prop 65 Notice

Aluminum Parallel Groove Clamp, Run: Cu & AL: 8 Sol. - 2/0, ACSR: 6 - 2/0, Tap: Cu & AL: 6 Sol. - 2/0, ACSR: 6 - 2/0

## Product Details

### General

Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	FASTAP™
UPC 12 Digit	7818106437788

### Dimensions

Dimension - Height inch	2.62 in
Dimension - Length Overall inch	1.62 in
Dimension - Pad Width inch	2.5 in
Dimension - Width inch	2.50 in

### Conductor Related

Conductor - AAAC 5005 Size	6 STR - 2/0 STR
Conductor - AAAC 5005 Size Range	6 STR - 2/0 STR
Conductor - AAAC 6201 Run	6 STR - 2/0 STR
Conductor - AAAC 6201 Size	6 STR - 2/0 STR
Conductor - AAAC 6201 Size Range	6 STR - 2/0 STR
Conductor - ACSR Str Size	6 STR - 2/0 STR
Conductor - ACSR Str Size A Range	6 Str. - 2/0
Conductor - ACSR Str Size B Range	6 Str. - 2/0
Conductor - AL Str Size A	8 SOL - 2/0 STR
Conductor - AL Str Size A Range	8 Sol. 2/0
Conductor - AL Str Size B	8 SOL - 2/0 STR
Conductor - AL Str Size B Range	8 Sol. - 2/0 Str.
Conductor - Copper Solid Size	#8 - 2/0
Conductor - Copper Solid Size Range	#8 - 2/0
Conductor - Copper Str Size A Range	8 Sol. 2/0
Conductor - Copper Str Size B Range	8 Sol. - 2/0 Str.

Conductor Type	<ul style="list-style-type: none"><li>• AAAC C 5005-Size</li><li>• AAAC C 6201-Size</li><li>• ACSR C Str-Size</li><li>• AL C Str-Size A</li><li>• AL C Str-Size B</li><li>• CU C Solid-Size</li><li>• CU C Str-Size A</li><li>• CU C Str-Size B</li><li>• CU Weld C Solid-Size</li></ul>
----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)