



## WCB47

by Burndy  
Catalog ID: WCB47

Prop 65 Notice

Wejtap Assembly , Installed With Blue Booster,Run:.684-.600,  
Tap:.684-.600.

Features: With Blue Power Booster, ANSI Class AA, Conductor Size (tap - Mm): 15 - 17 SQ-MM, Installation Tool: WTRB, WTY Tool, Booster: WPBB Box 25, Booster Color: Blue, Color Code: Blue, Cable Diameter Range (run): 0.6 - 0.684 IN, Conductor Type: Run: ACSR, AAC, Tap: ACSR, AAC, Copper, Conductor Size (run - Mm): 15 - 17 SQ-MM, Cable Diameter Range (tap): 0.6 - 0.684 IN

## Product Details

### General

Application	For use in tap applications using large run and tap conductor sizes
Connector Type	Tap
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810873755
UPC 12 Digit	7818108737555

### Dimensions

Dimension - F Width Center to Center inch	2 in
Dimension - G inch	1.1 in

### Conductor Related

Conductor - ACSR Str Run	266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Run Range	266.8 (18/1) Waxwing kcmil-336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Tap	266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Tap Range	266.8 (18/1) Waxwing kcmil-336.4 (18/1) Merlin kcmil
Conductor - AL Str Run	300 kcmil;336 kcmil;350 kcmil
Conductor - AL Str Run Range	300 kcmil-350 kcmil
Conductor - AL Str Tap	300 kcmil;336 kcmil;350 kcmil
Conductor - AL Str Tap Range	300 kcmil-350 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	25
-----------------------	----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)