



UCT32RSSS

by Burndy
Catalog ID: UCT32RSSS

Aluminum Parallel Groove Clamp, Run: Cu & AL: 1 Sol. - 400, ACSR: 2 - 336.4, Tap: Cu & AL: 8 Sol. - 4/0, ACSR: 6 - 4/0, Stainless hardware

Accommodates: Aluminum,Copper, ACSR, AAAC, ACAR,Steel wire.
Connector is not recommended for Copper to Copper applications

Product Details

General

Application	The system helps secure both the Tap and Run conductors while installing on primary, secondary and service lines. Connector is not recommended for Copper to Copper applications
Material	Aluminum
Plated	N
Plating Type	Unplated
Sub Brand	FASTAP
Trade Name	FASTAP™
Type	UCT
UPC	781810643884
UPC 12 Digit	7818106438844

Dimensions

Dimension - Height inch	2.62 in
Dimension - Length Overall inch	1.62 in
Dimension - Width inch	2.82 in

Conductor Related

Conductor - AAAC 5005 Size	6 STR - 336.4
Conductor - AAAC 5005 Size Range	6 STR - 336.4
Conductor - AAAC 6201 Size	6 STR - 336.4
Conductor - AAAC 6201 Size Range	6 STR - 336.4
Conductor - ACSR Str Size	6 STR - 336.4
Conductor - ACSR Str Size A Range	2 Str. - 336.4
Conductor - ACSR Str Size B Range	6 Str. - 4/0
Conductor - AL Str Size A	1 SOL - 400
Conductor - AL Str Size A Range	1 Sol. - 400
Conductor - AL Str Size B	8 SOL - 4/0 STR
Conductor - AL Str Size B Range	8 Sol. - 4/0 Str.
Conductor - Copper Solid Size	8-400
Conductor - Copper Solid Size Range	8-400
Conductor - Copper Str Size A Range	1 Sol. - 400

Conductor - Copper Str Size B Range	8 Sol. - 4/0 Str.
Conductor Type	• AAAC C 5005-Size • AAAC C 6201-Size • ACSR C Str-Size • AL C Str-Size A • AL C Str-Size B • CU C Solid-Size • CU C Str-Size A • CU C Str-Size B • CU Weld C Solid-Size

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)