

# YOT37R37R

by Burndy  
Catalog ID: YOT37R37R

Prop 65 Notice

Tap Conductor, 261,318,M Index



## Product Details

### General

Connector Type	Tap
Die Index Run Side	261;318;M
Die Index Tap Side	261;318;M
Material	Aluminum Alloy
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYTEE™
UPC	781810016091
UPC 12 Digit	7818100160911

### Dimensions

Dimension - Height fraction	6-3/8 in
Dimension - Height inch	6.375 in
Dimension - L Length Overall mm	318 mm
Dimension - Length Overall inch	12.50 in

### Conductor Related

Conductor - AAAC 5005 Run	30.58 (7) kcmil
Conductor - AAAC 5005 Run Range	30.58 (7) kcmil
Conductor - AAAC 5005 Tap	30.58 (7) kcmil
Conductor - AAAC 5005 Tap Range	30.58 (7) kcmil
Conductor - AAAC 6201 Run	30.58 (7) kcmil
Conductor - AAAC 6201 Run Range	30.58 (7) kcmil
Conductor - AAAC 6201 Tap	30.58 (7) kcmil
Conductor - AAAC 6201 Tap Range	30.58 (7) kcmil
Conductor - ACSR Str Run	477.0 (26/7) Hawk kcmil;477. (30/7) Hen kcmil;500.0 (30/7) Heron kcmil;556.5 (24/7) Parakeet kcmil
Conductor - ACSR Str Run Range	477.0 (26/7) Hawk kcmil-556.5 (24/7) Parakeet kcmil
Conductor - ACSR Str Tap	477.0 (24/7) Flicker kcmil;477.0 (26/7) Hawk kcmil;477. (30/7) Hen kcmil;500.0 (30/7) Heron kcmil;556.5 (24/7) Parakeet kcmil
Conductor - ACSR Str Tap Range	477.0 (24/7) Flicker kcmil-556.5 (24/7) Parakeet kcmil

Conductor - AL Str Run	556 kcmil
Conductor - AL Str Run Range	556 kcmil
Conductor - AL Str Tap	556 kcmil
Conductor - AL Str Tap Range	556 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	4
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)