

YA27L3G1

by Burndy
Catalog ID: YA27L3G1

COPPER COMPRESSION TERMINAL.



Product Details

General

Color Code	Orange
Connector Type	Terminal
Die Index	14
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810461150
UPC 12 Digit	7818104611500

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - D inch	0.70 in
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	55 mm
Dimension - Length Overall inch	2.16 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.62 in
Dimension - Pad Width inch	0.91 in
Dimension - Strip Length inch	1-1/16
Dimension - Stud Size inch	5/16

Dimension - Thread Size	5/16 in
Dimension - Z inch	0.36 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	150 (61) Navy
Conductor - Copper Str Navy Size Range	150 (61) Navy
Conductor - Copper Str Size	3/0 AWG
Conductor - Copper Str Size Range	3/0 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)