



YTU25R4W

by Burndy
Catalog ID: YTU25R4W

Prop 65 Notice

Al Compression T-Tap Connector, 1/0 AWG ACSR/Al/Cu(Run), #6 ACSR,6201,5005, #4 AWG, #4 Sol. Al/Cu(Tap)

Product Details

General

Connector Type	Tap
Die Index Run Side	C
Die Index Tap Side	BG
Material	Aluminum Alloy
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	Y
UPC	781810155004
UPC 12 Digit	7818101550044

Dimensions

Dimension - Height fraction	2-3/8 in
Dimension - Height inch	2.375 in
Dimension - L Length Overall mm	124 mm
Dimension - Length Overall inch	4.875 in

Conductor Related

Conductor - AAAC 5005 Run	123.3 (7) kcmil
Conductor - AAAC 5005 Run Range	123.3 (7) kcmil
Conductor - AAAC 5005 Tap	30.58 (7) kcmil
Conductor - AAAC 5005 Tap Range	30.58 (7) kcmil
Conductor - AAAC 6201 Run	123.3 (7) kcmil
Conductor - AAAC 6201 Run Range	123.3 (7) kcmil
Conductor - AAAC 6201 Tap	30.58 (7) kcmil
Conductor - AAAC 6201 Tap Range	30.58 (7) kcmil
Conductor - ACSR Cmpt Run	1/0 AWG
Conductor - ACSR Cmpt Run Range	1/0 AWG
Conductor - ACSR Cmpt Tap	6 AWG
Conductor - ACSR Cmpt Tap Range	6 AWG
Conductor - ACSR Str Run	80 (8/1) Grouse kcmil
Conductor - ACSR Str Run Range	80 (8/1) Grouse kcmil

Conductor - AL Str Run	1/0 AWG
Conductor - AL Str Run Range	1/0 AWG
Conductor - AL Str Tap	4 AWG
Conductor - AL Str Tap Range	4 AWG
Conductor - Copper Solid Tap	4 AWG
Conductor - Copper Solid Tap Range	4 AWG
Conductor - Copper Str Run	1/0
Conductor - Copper Str Run Range	1/0
Conductor - Copper Str Tap	4 AWG
Conductor - Copper Str Tap Range	4 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)