

YAV25L2NT516FX

by Burndy
Catalog ID: YAV25L2NT516FX

Prop 65 Notice

Copper Compression Lug, Narrow Tongue, 2 Holes W/ Inspection Window, 1/0 AWG, 5/16" Stud, 12 index, Pink, Tin plated



Product Details

General

Color Code	Pink
Connector Type	Terminal
Die Index	12
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810498040

Dimensions

Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.69 in
Dimension - D inch	1.71 in
Dimension - Diameter Min Size inch	1.71 in
Dimension - Hole Size inch	0.33 in
Dimension - L Length Overall mm	72 mm
Dimension - Length Overall inch	2.82 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.58 in
Dimension - Strip Length inch	11/16
Dimension - Stud Size inch	5/16

Dimension - Z inch	0.37 in
--------------------	---------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	1/0 (275/#24)
Conductor - Copper DLO Size Range	1/0 (275/#24)
Conductor - Copper Flex G Size	1/0
Conductor - Copper Flex G Size Range	1/0
Conductor - Copper Flex H Size	1/0
Conductor - Copper Flex H Size Range	1/0
Conductor - Copper Flex I Size	1/0
Conductor - Copper Flex I Size Range	1/0
Conductor - Copper Flex K Size	1/0
Conductor - Copper Flex K Size Range	1/0
Conductor - Copper Flex M Size	1/0

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)