

YCS361R

by Burndy
Catalog ID: YCS361R

Prop 65 Notice

HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), Index: 327.

Features: HYSPLICE Sleeve Designed To Withstand Jumper Loop Tensile And Vibration Stresses, Made Of Aluminum With Staked-In Cable Stop, Installed With Same Die As Equivalent Fulltension Sleeves, Pre-Filled With PENETROX Joint Compound, Die Index: 327 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U327 Die, (6), Y45 Tool, U327 Die With PT-6515 Adapter, (6), Y46 Tool, U327 Die With PUADP-1 Adapter, (6), Y48B Tool, C327 Die, (2), Y60BHU Tool, L327 Die, (2), Conductor Type: ACSR, 6201, 5005, Aluminum



Product Details

General

Application	For ACSR, All Aluminum, 6201, 5005 And Compressed Conductors
Connector Type	Splice
Die Index	327
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YCS-R
UPC	781810820575
UPC 12 Digit	7818108205755

Dimensions

Dimension - B Length fraction	4-3/50 in
Dimension - B Length inch	4.06 in
Dimension - L Length Overall mm	210 mm
Dimension - Length Overall inch	8.25 in
Dimension - Outside Diameter inch	1.3 in

Conductor Related

Conductor - ACSR Str Size	477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Size Range	477.0 (18/1) Pelican kcmil
Conductor - AL Str Size	477 kcmil (18/1)
Conductor - AL Str Size Range	477 kcmil

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)