



# Pole Base Foundation, 6-5/8" OD x 60" Long

By CHANCE Utility  
Catalog # [C11232JG4VL](#)

Streetlight Foundation (SLF) 6.625 OD x 60" Long, 1" thick x 12" square baseplate, variable circle, hardware included.



\*Representative Image

## Features

- Variable 9" - 14" Bolt Circle
- 4 slots, 1" Dia x 4" Long
- Suitable for Streetlight, Roadway, and Architectural Lighting
- Other applications include EV Charging Infrastructure, 5G/6G Poles, Rail Applications, End Zone Tower Systems, Solar Array Pole Mount, and Signage

## Application

Helical Anchoring

## General

Base Plate Shape	Square
Bolt Hole Type	Slotted
Coating	Galvanized
EU RoHS Indicator	No
Ground Lug Hole	No
Hardware Packaging	Installed
Number of Bolt Slots	4
Pipe Type	Round Pipe
Type	Lighting Foundation Anchors
UPC	096359010227
With Hardware	Included

## Dimensions

Base Plate Dimensions	12.00 in
Base Plate Thickness	1.000 in
Bolt Length	4.00 in
Cableway Distance From Base	12 in
Cableway Length	12.00 in
Cableway Width	2.50 in
Center hole dimensions	5.00 in
Diameter - Bolt	1 in
Diameter - Bolt Circle	<ul style="list-style-type: none"> <li>• 9 in</li> <li>• 14 in</li> </ul>

Dimensions	60.00 in x 12.000 in x 12.000 in
Foundation Diameter	6.630 in
Foundation Length	60 in
Height	12.000 in
Length	60.00 in
Weight	137.000 lb
Width	12.000 in

## Logistics

Pallet Quantity	9
Standard Package	1

## Product Assets

- [Case Studies - Case History - Randazzo Park \(CH04318E\\_1120\)](#)
- [Catalogs - CHANCE Instant Foundations - Product Catalog \(CA04140E\)](#)
- [Engineering Drawing - 9" - 14" B.C. Lighting Foundation 6" X 60"](#)
- [Installation Manuals - Instant Foundations \(TD04365E\)](#)
- [Literature - Instant Foundation Solutions \(SF04248E\\_0819\)](#)
- [Literature - Precast Concrete Collars \(SF04273E\)](#)
- [Literature - Instant Foundations® for EV Charging Stations \(SF04048E\)](#)
- [Literature - Instant Foundations and Pre-Cast Concrete Collars \(BR04331E\)](#)
- [Sales Drawings - 9" - 14" B.C. Lighting Foundation 6" X 60"](#)
- [Test Documents - Pole Load Determination Data Sheet \(TD04196E\)](#)
- [Video - CHANCE Instant Foundation & Concrete Collar \(VI04163E0520\)](#)
- [Video - SLF \(VI04173E1021\)](#)
- [Video - CHANCE® Instant Foundation System \(VI04150E\\_14L\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-C11232JG4VL-SPEC-EN | REV 1/2024