



Pole Base Foundation, 8-5/8" OD x 60" Long

By CHANCE Utility
Catalog # C11242NG4VP

Streetlight Foundation (SLF) 8.625 OD x 60" Long, 1" thick x 15.75" square baseplate, variable circle, hardware included.



*Representative Image

Features

- Variable 11-1/2" - 17" Bolt Circle
- 4 slots, 1" Dia x 4" Long
- Suitable for Streetlight, Roadway, and Architectural Lighting
- Other applications include EV Charging Infrastructure, 5G/6G Poles, Rail Applications, End Zone Tower Systems, Solar Array Pole Mount, and Signage

Application

Helical Anchoring

General

Base Plate Shape	Square
Bolt Hole Type	Slotted
Coating	Galvanized, ASTM A-153
EU RoHS Indicator	No
Ground Lug Hole	No
Hardware Packaging	Taped to Shaft
Number of Bolt Slots	4
Pipe Type	Round Pipe
Type	Lighting Foundation Anchors
UPC	096359010272
With Hardware	Included

Dimensions

Base Plate Dimensions	15.75 in
Base Plate Thickness	1.000 in
Bolt Length	4.00 in
Cableway Distance From Base	12 in
Cableway Length	12.00 in
Cableway Width	2.50 in
Center hole dimensions	7.00 in
Diameter - Bolt	1 in
Diameter - Bolt Circle	• 11 in • 17 in

Dimensions	60.00 in x 16.000 in x 16.000 in
Foundation Diameter	8.630 in
Foundation Length	60 in
Height	16.000 in
Length	60.00 in
Weight	187.000 lb
Width	16.000 in

Logistics

Pallet Quantity	9
Standard Package	1

Product Assets

- [Case Studies - Case History - Randazzo Park \(CH04318E_1120\)](#)
- [Catalogs - CHANCE Instant Foundations - Product Catalog \(CA04140E\)](#)
- [Engineering Drawing - 11" - 17" B.C. Lighting Foundation 8" X 60"](#)
- [Installation Manuals - Instant Foundations \(TD04365E\)](#)
- [Literature - Instant Foundation Solutions \(SF04248E_0819\)](#)
- [Literature - Precast Concrete Collars \(SF04273E\)](#)
- [Literature - Instant Foundations® for EV Charging Stations \(SF04048E\)](#)
- [Literature - Instant Foundations and Pre-Cast Concrete Collars \(BR04331E\)](#)
- [Sales Drawings - 11" - 17" B.C. Lighting Foundation 8" X 60"](#)
- [Technical Solutions - CH-C11242NG4VP-SPEC-EN](#)
- [Test Documents - Pole Load Determination Data Sheet \(TD04196E\)](#)
- [Video - CHANCE Instant Foundation & Concrete Collar \(VI04163E0520\)](#)
- [Video - SLF \(VI04173E1021\)](#)
- [Video - CHANCE® Instant Foundation System \(VI04150E_14L\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-C11242NG4VP-SPEC-EN | REV 1/2024