



Anchor, Tool, SS175 Drive Wrench

By CHANCE Utility
Catalog # C3030195

SS175 Drive Tool for use with 7 5/8" (193.7mm) bolt circle Kelly Bar Adapter.



Features

- These tools include our proprietary Alignment Window that helps reduce chance of finger pinch when anchor is inserted into tool.
- These drive tools require the appropriate Kelly bar adapter, sold separately
- Each comes with bolts, nuts and lockwashers.
- Includes Bent Arm Pin and Coil Lock

Application

Anchor/Pile Installation

General

Attachment Style	Kelly Bar Adapter
Bolt Grade	2
Coating	Painted
Drive Wrench Anchor Type	SS175 Anchor
EU RoHS Indicator	No
Number of Bolt Holes	12
Torque Rating	10500 ft-lbs
Type	Anchor/Pile Installation Tools
UPC	096359014997

Dimensions

Anchor Installation Hole Size	0.625 in
Diameter - Bolt	0.625 in
Diameter - Bolt Circle	7.625 in
Dimensions	12.19 in x 12.190 in x 6.560 in
Height	6.560 in
Length	12.19 in
Weight	19.600 lb
Width	12.190 in

Logistics

Pallet Quantity	27
Standard Package	1

Product Assets

- [Catalogs - Anchor Tools \(4A_CA06122E\)\)](#)
- [Installation Manuals - Instructions for CHANCE Bolted Helical Pile Drive Tools](#)
- [Installation Manuals - TD06132E_Type_SS_and_RR_Anchors](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Literature - CHANCE Anchor Installation Tools: Product Feature & Selection Guide \(BR06167E\)](#)
- [Literature - SF04364E Digital Torque Indicator](#)
- [Sales Drawings - Anchor Wrench \(SA3031502\)](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
- [Video - Square Shaft Anchor Drive Wrench](#)
- [Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)

Related Products

- [C3031225 - Anchor, Tool, Bent Arm Pin, 3/4in X 3.5in](#)
- [PSZ0012557P - Anchor Tool Bolt](#)
- [PSZ0012552P - Anchor Tool Nut](#)
- [PSZ0012553P - Anchor Tool Lockwasher](#)



A proud member of the Hubbell Family.