



# Anchor, Tool, SS225 Drive Wrench

By CHANCE Utility  
Catalog # C3030202

SS225 Drive Tool for use with 7 5/8" (193.7mm) bolt circle  
Kelly Bar Adapter.



\*Representative Image

## Features

- These tools include our proprietary Alignment Window that helps reduce chance of finger pinch when anchor is inserted into tool.
- These drive tools require the appropriate Kelly bar adapter, sold separately
- Each comes with bolts, nuts and lockwashers.
- Includes Bent Arm Pin and Coil Lock

## Application

Anchor/Pile Installation

## General

Attachment Style	Kelly Bar Adapter
Bolt Grade	2
Coating	Painted
Drive Wrench Anchor Type	SS225 Anchor
EU RoHS Indicator	No
Number of Bolt Holes	12
Torque Rating	21000 ft-lbs
Type	Anchor/Pile Installation Tools
UPC	096359015017

## Dimensions

Anchor Installation Hole Size	0.625 in
Diameter - Bolt	0.625 in
Diameter - Bolt Circle	7.625 in
Weight	29.400 lb

## Logistics

Pallet Quantity	20
Standard Package	1

## Product Assets

- [Catalogs - Anchor Tools \(4A\\_CA06122E\)\)](#)
- [Installation Manuals - Instructions for CHANCE Bolted Helical Pile Drive Tools](#)
- [Installation Manuals - TD06132E\\_Type\\_SS\\_and\\_RR\\_Anchors](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Literature - CHANCE Anchor Installation Tools: Product Feature & Selection Guide \(BR06167E\)](#)
- [Literature - SF04364E Digital Torque Indicator](#)
- [Sales Drawings - Anchor Wrench \(SA3031502\)](#)
- [Technical Solutions - CH-C3030202-SPEC-EN](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
- [Video - Square Shaft Anchor Drive Wrench](#)
- [Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)

## Related Products

- [C3031224 - Anchor, Tool, Bent Arm Pin, 1in X 4.5in](#)
- [PSZ0012553P - Anchor Tool Lockwasher](#)
- [PSZ0012557P - Anchor Tool Bolt](#)
- [PSZ0012552P - Anchor Tool Nut](#)



A proud member of the Hubbell Family.