



# 15 kV, 110 kV BIL, Type C Loadbreak Polymer Cutout / Arrester Combination w/200A 12kAIC fuseholder

By CHANCE Utility  
Catalog # [CP73FL143EB](#)

15 kV, 110 kV BIL, Loadbreak Type C Polymer Cutout / Arrester Combination with a 200A, 12kAIC fuseholder, small eyebolt connector and a NEMA "B" crossarm bracket.



\*Representative Image

## Features

- Fully compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP ( Enhanced Silicone Polymer ) Insulating Material
- TDG ( Thermal Diffusion Galvanization ) Insulator Assembly Castings
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings
- Non Interchangeable Mounting Assembly

## General

|                                       |                                  |
|---------------------------------------|----------------------------------|
| Bracket Type                          | NEMA "B" Heavy Duty for crossarm |
| Description - Replacement Fuse Holder | T730-143T                        |
| Type                                  | Cutout                           |

## Electrical Ratings

|                                   |  |
|-----------------------------------|--|
| BIL                               | 110 kV   |
| Creep and Leakage Distance        | 12.6" (319mm)                                      |
| Current Rating                    | 200 A  |
| Fuselink Current Range            | 140A to 200A - removable buttonhead fuse link only |
| Reference Voltage Limit - Minimum | Thru 14.4kV  |
| Temperature Rise - Max. at 300A   | 39° C  |
| Voltage - Maximum                 | 15 kV  |
| Voltage - Radio Interference      | Ambient @ 9.41kV                                   |
| Voltage Rating                    | 15 kV  |

## Logistics

|                  |   |
|------------------|---|
| Standard Package | 1 |
|------------------|---|

## Product Assets

- [Catalogs - Type C-Polymer Cutouts \(10AA\)](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Sales Drawings - 110KV BIL Polymer Cutout/ Arrester \(SAP73DL1\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-CP73FL143EB-SPEC-EN | REV 1/2024