

# Insulated Ratchet Cable Cutter For 556 kcmil ACSR, 6'

By Chance Lineman Tools & Equipment  
Catalog # [C4031382](#)

RATCHET WIRE CUTTER - 6FT - 556ACSR, High-performance design incorporates Delrin plastic rollers and a two-piece operating rod. Roller mechanism travels smoothly along main Epoxiglas™ pole. Linked through the roller support unit, the hinged operating rod and larger Epoxiglas pole reinforce each other. These Ratchet Cable Cutters meet OSHA Electrical Rating subpart V-section 1926.951 (d). Insulated support pole is orange 112"-diameter Epoxiglas with Plastisol butt cap, operating shaft is 38"-diameter solid fiberglass rod, and lever handle is 1"-diameter Epoxiglas with rubber cushion grip.

## Features

- Designed for easier operation
- Tested per OSHA & ASTM F711
- High-performance design incorporates Delrin rollers and two-piece operating rod
- Roller mechanism travels smoothly along main Epoxiglas™ pole
- Linked through the roller support unit, the hinged operating rod and larger Epoxiglas pole reinforce each other
- Meet OSHA Electrical Rating subpart V-section 1926.951 (d)
- Insulated support pole is Chance orange 1-1/2"-diameter Epoxiglas with Plastisol butt cap
- Operating rod is 3/8"-diameter solid fiberglass rod
- Lever handle is 1"-diameter Epoxiglas with rubber cushion grip
- Four standard models offer practical 6-foot or 8-foot lengths with choice of cutter heads for soft wire or ACSR
- Shear-type steel blades cut without deforming cable
- Heads are interchangeable for field changeouts
- Soft-Wire Head cuts aluminum cable through 1000 kcmil bare (1.152") or jacketed URD (2.125") and copper through 556 kcmil (1")
- Spare cutters may be ordered separately

## General

Catalog Number C4031382



\*Representative Image

EU RoHS Indicator	No
Storage Bag Included?	T306-0028 (Bag not included. Must be ordered separately.)
UPC	096359019053

## Dimensions

Dimensions	72 in x 12 in x 1.5 in
Height	1.5 in
Length	72 in
Weight	13.72 lb
WeightMetric	6.2 kg
Width	12 in

## Conductor Related

Conductor Size	556 MCM ACSR
----------------	--------------

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

## Product Assets

[Catalogs - Cutters](#)  
[Installation Manuals - CHANCE® Epoxiglas™ Live-Line Tool](#)  
[Instruction Manual](#)  
[Sales Drawings - Ratchet Cable Cutters](#)  
[Specifications - C4031382](#)