

Insulated Ratchet Cable Cutter For 1000 kcmil A.A. / 500 kcmil Cu, 8'

By Chance Lineman Tools & Equipment
Catalog # [C4031383](#)



*Representative Image

RATCHET WIRE CUTTER - 8FT - 1000AA+500CU, High-performance design incorporates Delrin plastic rollers and a two-piece operating rod. Roller mechanism travels smoothly along main Epoxiglas™ pole. Linked through the roller support unit, the hinged operating rod and larger Epoxiglas pole reinforce each other. These Ratchet Cable Cutters meet OSHA Electrical Rating subpart V-section 1926.951 (d). Insulated support pole is orange 1 1/2"-diameter Epoxiglas with Plastisol butt cap, operating shaft is 3/8"-diameter solid fiberglass rod, and lever handle is 1"-diameter Epoxiglas with rubber cushion grip.

Features

- Designed for easier operation
- Tested per OSHA & ASTM F711
- High-performance design incorporates Delrin rollers and two-piece operating rod
- Roller mechanism travels smoothly along main Epoxiglas™ pole
- Linked through the roller support unit, the hinged operating rod and larger Epoxiglas pole reinforce each other
- Meet OSHA Electrical Rating subpart V-section 1926.951 (d)
- Insulated support pole is Chance orange 1-1/2"-diameter Epoxiglas with Plastisol butt cap
- Operating rod is 3/8"-diameter solid fiberglass rod
- Lever handle is 1"-diameter Epoxiglas with rubber cushion grip
- Four standard models offer practical 6-foot or 8-foot lengths with choice of cutter heads for soft wire or ACSR
- Shear-type steel blades cut without deforming cable
- Heads are interchangeable for field changeouts
- Soft-Wire Head cuts aluminum cable through 1000 kcmil bare (1.152") or jacketed URD (2.125") and copper through 556 kcmil (1")
- Spare cutters may be ordered separately

General

EU RoHS Indicator	No
Storage Bag Included?	T306-0029 (Bag not included. Must be ordered separately.)
UPC	096359019060

Dimensions

Length	96 in
Weight	16.7 lb
WeightMetric	7.5 kg

Conductor Related

Conductor Size	1000 MCM A.A. / 500 MCM Cu.
----------------	-----------------------------

Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)
[Sales Drawings - Ratchet Cable Cutters](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CLTE-C4031383-SPEC-EN | REV 6/2024