



# Heavy Duty Adjustable Stick with Disconnect-Style NEMA Head 10 ft to 14 ft (3.0 to 4.2 m)

By Chance Lineman Tools & Equipment  
Catalog # [C4032600](#)



HD ADJ STICK W/DISC, NEMA HEAD, 10'-14', Clearly marked at each 1-foot extension lock, one of these tools can replace as many as eight single-length hotsticks. Especially for such tight confines as substations, these adjustable sticks can be stored in standard-length cannisters and avoid the difficulties of working extra-long sticks through busswork structures. Classified as Heavy-Duty due to its large (1.25"-diameter) insulated top section and 1.5"-O.D. epoxy-reinforced fiberglass base tube.

## Features

- Tested per OSHA & ASTM F711
- For substations and close-clearance worksites
- Clearly marked at each 1' extension lock
- One of these tools can replace as many as eight singlelength hotsticks
- Adjustable sticks can be stored in short collapsed lengths and to avoid difficulties of maneuvering extra-long sticks through busswork structures
- Heavy-duty construction - Classified as Heavy-Duty due to its large (1-1/4"-diameter) insulated top section and 1-1/2"-O.D. epoxy-reinforced fiberglass base tube
- 24" overlap at usable-length extremes - In each size, a 2' section of Epoxiglas™ foam-core top section remains inside the base section at the longest locked, usable length and At the shortest locked length, insulated top section extends a full 2' beyond base

## General

Catalog Number	C4032600
EU RoHS Indicator	No
Storage Bag Included?	P621-8 (Bag not included. Must be ordered separately.)
Style	Disconnect Head
UPC	096359020110

## Dimensions

Dimensions	168 in x 6 in x 6 in
Dimensions Metric	426.7 mm x 15.2 mm x 15.2 mm
Height	6 in
Height Metric	15.2 mm
Length	168 in
Length - Retracted	8.2 ft
Length - Retracted Metric	2.4 m
Length Metric	426.7 mm
Lengths - Extended	<ul style="list-style-type: none"><li>• 10</li><li>• 11</li><li>• 12</li><li>• 13</li><li>• 14</li></ul>
Weight	10 lb
WeightMetric	4.5 kg
Width	6 in
WidthMetric	15.2 mm

## Certifications And Compliance

Buy America(n) Qualified      Contact Manufacturer

## Product Assets

- [Catalogs - Insulated Hand Tools](#)
- [Installation Manuals - CHANCE® Epoxiglas™ Live-Line Tool](#)
- [Instruction Manual](#)
- [Sales Drawings - Adjustable Substation Stick](#)
- [Specifications - C4032600](#)