

Heavy Duty Telescoping Disconnect Stick 25 ft (7.6 m) Maximum Length

By Chance Lineman Tools & Equipment
Catalog # [C4031601](#)



TELESCOPING TOOL, 25' H D, The Telescoping Tools offer maximum convenience. The universal end fitting on the insulated top section accepts a wide variety of attachments so that the lineman can disconnect switches, replace cutout tubes and reclose, remove pole covers, prune trees and complete many other overhead tasks . . . all with one tool.

*Representative Image

Features

- Tested per OSHA & ASTM F711
- Allow linemen to perform many routine jobs from ground level
- Universal end fitting on insulated top section accepts a wide variety of attachments
- This allows lineman to disconnect switches and replace cutout tubes
- Also allows lineman to remove pole covers, prune trees, plus other overhead tasks
- Sticks retract to approximately 5 ft. for easy truck transport (even in most cab sections)
- Heavy-duty, spring-loaded plastic buttons keep extended tool sections locked in place
- As each section extends and slightly twists, buttons also pop securely into place
- Heavy-duty units have slightly larger tip sections: 1-1/4" versus 1-1/8"
- Each heavy-duty telescoping tube is also slightly larger
- This results in more rigidity, important for managing heavyweight maintenance tasks
- Both tip sections feature proven Chance Epoxiglas™
- This unicellular foam-core material prevents moisture trapping voids between foam and tool

General

Catalog Number	C4031601
Duty	Heavy Duty
EU RoHS Indicator	No
Storage Bag Included?	P6215 (Bag not included. Must be ordered separately.)
Style	Telescoping Disconnect Tool

UPC

096359019282

Dimensions

Diameter	2.25 in
Dimensions	67 in x 4.38 in x 4.38 in
Dimensions Metric	170.2 mm x 11.1 mm x 11.1 mm
Height	4.38 in
Height Metric	11.1 mm
Length	67 in
Length - Retracted	5.25 ft
Length - Retracted Metric	1.6 m
Length Metric	170.2 mm
Lengths - Extended	<ul style="list-style-type: none"> • 16.5 ft • 20.5 ft • 25 ft
Mounting Bolt Spacing	096359019282
Weight	12.3 lb
WeightMetric	5.5 kg
Width	4.38 in
WidthMetric	11.1 mm

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Product Assets

- [Catalogs - Insulated Hand Tools](#)
- [Installation Manuals - CHANCE® Epoxiglas™ Live-Line Tool](#)
- [Instruction Manual](#)
- [Sales Drawings - Telescopic Hotstick](#)
- [Specifications - C4031601](#)