



## Wire-Ready Foundation, 10-3/4" OD x 84" Long

By CHANCE Foundation Solutions  
Catalog # [T1120590](#)

Streetlight Foundation (SLF) 10.75 OD x 84" Long, 1" thick x 15-3/4" square baseplate, variable circle, hardware included.



\*Representative Image

### Features

- Variable 13-1/2" - 17" Bolt Circle
- 4 holes, 1" Dia x 5" Long
- hardware included
- Suitable for Streetlight, Roadway, and Architectural Lighting
- Other applications include EV Charging Infrastructure, 5G/6G Poles, Rail Applications, End Zone Tower Systems, Solar Array Pole Mount, and Signage

### Application

Helical Anchoring

### General

Base Plate Shape	Square
Bolt Hole Type	Slotted
Coating	Galvanized, ASTM A-153
EU RoHS Indicator	No
Ground Lug Hole	No
Hardware Packaging	Installed
Number of Bolt Slots	4
Pipe Type	Round Pipe
Type	Lighting Foundation Anchors
UPC	096359241539
With Hardware	Included

### Dimensions

Base Plate Dimensions	15.75 in
Base Plate Thickness	1.000 in
Bolt Length	4.00 in
Cableway Distance From Base	12 in
Cableway Length	12.00 in
Cableway Width	2.50 in
Center hole dimensions	7.00 in
Diameter - Bolt	1 in
Diameter - Bolt Circle	<ul style="list-style-type: none"><li>• 13.5 in</li><li>• 17 in</li></ul>
Foundation Diameter	10.750 in
Foundation Length	84 in
Weight	280.000 lb

### Logistics

Pallet Quantity	6
Standard Package	1

### Product Assets

[Case Studies - Case History - Randazzo Park \(CH04318E\\_1120\)](#)  
[Engineering Drawing - 13-1/2" - 17" B.C. Lighting Foundation 10" X 84"](#)  
[Installation Manuals - Instant Foundations \(TD04365E\)](#)  
[Literature - Instant Foundation Solutions \(SF04248E\\_0819\)](#)  
[Literature - Precast Concrete Collars \(SF04273E\)](#)  
[Literature - Instant Foundations and Pre-Cast Concrete Collars \(BR04331E\)](#)  
[Literature - Instant Foundations® for EV Charging Stations \(SF04048E\)](#)  
[Sales Drawings - 13-1/2" - 17" B.C. Lighting Foundation 10" X 84" \(SA112-0590\\_C\)](#)  
[SDS - MSDS - Galvanized Steel Products](#)  
[Test Documents - Pole Load Determination Data Sheet \(TD04196E\)](#)  
[Video - CHANCE Instant Foundation & Concrete Collar \(VI04163E0520\)](#)  
[Video - SLF \(VI04173E1021\)](#)  
[Video - CHANCE® Streetlight Foundation \(VI04147E0719\)](#)

### Related Products

[C3030684](#)



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
CN-T1120590-SPEC-EN | REV 1/2024