

# HUBBELL® Premise Wiring



## FIBERHUBB™ Splice Cassettes

Hubbell Premise Wiring's FIBERHUBB Splice Cassettes are designed to support mission-critical fiber applications, such as data center interconnects and backbones, local area networks, and enterprise campus applications. Featuring a brand new design these cassettes are all metal construction with integrated cable management, removable front plate, and shuttered adapters for maximum protection inside one LGX footprint!

The cassettes save installers valuable time, requiring fewer components and allowing fiber to be spliced in front of the enclosure where more space is available rather than inside the enclosure. Fiber distribution cable can be brought directly to the cassette and all splicing can easily be done and housed inside the cassette body. FIBERHUBB Splice Cassettes reduce costs and the total number of components, eliminating the need for separate splice trays, adapter panels, and pigtail bundles.

### Features & Benefits

- Includes: cassette housing, splice trays, loaded shuttered, adapter panel, pigtails, zip ties, velcro, splice holder
- Replaces FSP adapter panels, splice trays and pigtail bundles
- Enhanced management of pigtails and fiber slack
- Multiple DIN rail mounting locations
- Simplified ordering with one part number
- Cleaner installations and quicker repairs
- Installation flexibility for small fiber requirements



Standard Splice Cassettes

Adapter Type	Fiber Type	Fiber Stand Count	Adapter Color	Catalog No.
LC	OM3/OM4	12	Aqua	<a href="#">OCSPLCD12MM</a>
	OS2	12	Blue	<a href="#">OCSPLCD12SM</a>
	OM3/OM4	6	Aqua	<a href="#">OCSPLCD6MM</a>
	OS2	6	Blue	<a href="#">OCSPLCD6SM</a>
	OM3/OM4	24	Aqua	<a href="#">OCSPLCQ24MM</a>
	OS2	24	Blue	<a href="#">OCSPLCQ24SM</a>
LC/APC	OS2 SM	6	Green	<a href="#">OCSPLCDA6SM</a>
		12	Green	<a href="#">OCSPLCDA12SM</a>
SC/APC	OS2	6	Green	<a href="#">OCSPLCA6SM</a>
		12	Green	<a href="#">OCSPLCA12SM</a>
SC	OM3/OM4	12	Aqua	<a href="#">OCSPLCD12MM</a>
	OS2	12	Blue	<a href="#">OCSPLCD12SM</a>
	OM3/OM4	6	Aqua	<a href="#">OCSPLCD6MM</a>
	OS2	6	Blue	<a href="#">OCSPLCD6SM</a>



OCSPLCD12MM



OCSPLCQ24MM



OCSPLCD12SM



OCSPLCDA12SM



Ribbon Splice Cassettes

Adapter Type	Fiber Type	Fiber Stand Count	Adapter Color	Catalog No.
LC	OS2 SM	12	Blue	<a href="#">OCSPLCD12SMR</a>
		24	Blue	<a href="#">OCSPLCQ24SMR</a>
		24	Green	<a href="#">OCSPLCQA24SMR</a>
	OM3/OM4	12	Aqua	<a href="#">OCSPLCD12MMR</a>
		24	Aqua	<a href="#">OCSPLCQ24MMR</a>
		24	Aqua	<a href="#">OCSPLCQ24MMR</a>