


HUBBELL

Power Systems

Stirrup, Extruded Type

By FARGO
Catalog # [GH284AL](#)

Overhead Stirrup, Bolted, Stirrup, Extruded, Aluminum, AAC|AAAC|ACSR, Range 0.368 - 0.806 in



*Representative Image

Features

Extruded shape develops vibration proof connection.

General

Bolt Installation Torque (Recommended)	300 in-lbs
Catalog Number	GH284AL
Hot Stick Eyes	Yes
Inhibitor Loaded	Yes
Material	Aluminum Alloy
Material - Bail	Copper
Material - Body	Aluminum Alloy
Material - Eystem	Aluminum Alloy
Material - Keeper	Aluminum Alloy
Material - Stirrup	Copper
Number of Hot Stick Eyes	1
Plating	No
Style	Extruded Aluminum
Type	Stirrups
UPC	096359310556

Dimensions

Copper Loop Size	0.625 in
Diameter - Bolt	0.5 in
Diameter - Stirrup Nominal Wire	2/0 Solid
Dimensions	4.000 in x 5.500 in x 6.000 in
Height	6 in
Length	4 in
Weight	1.16 lb
Width	5.5 in
Width - Main Contact	2.4375 in

Conductor Related

Conductor Compatibility

ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;ACSR-Pigeon-3/0-6/1;ACSR-Penguin-4/0-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Brahma-203.2-16/19;AAC-Peachbell-6-7;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Daffodil-350-19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAAC 6201 Alloy-Akron-30.58-6/18;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18;AAAC 6201 Alloy-Anaheim-155.4-6/18;AAAC 6201 Alloy-Amherst-195.7-6/18;AAAC 6201 Alloy-Alliance-246.9-6/18

Conductor Diameter - Maximum	0.806
Conductor Diameter - Minimum	0.368
Conductor Diameter Range	0.368 - 0.806

Logistics

Packaging Type	Bag
Pallet Quantity	800

Product Assets

[Catalogs - Distribution Connectors](#)

[Sales Drawings - CC-25764](#)

[Video - Hubbell Power Systems Hotline Tap Clamps and Stirrup Clamps](#)

[Video - Hubbell Power Systems In Depth: Stirrup Clamps](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
FG-GH284AL-SPEC-EN | REV 6/2024