



## Indoor Rugged Telephone - VoIP (Keypad)

By GAI-Tronics  
Catalog # [246-710](#)

GAI-Tronics' SIP compatible Handset VoIP Surface-mount Telephones are designed to provide direct point-to-point communications between personnel throughout a facility over an existing LAN. The VoIP telephones are intended for connection to a 10/100 BaseT Ethernet SIP network and operate using power-over-Ethernet or an external power source. VoIP telephones are compatible with Cisco's UCM Version 5.0 or newer.



## Features

- High-impact, Non-metallic Enclosure
- Embedded Browser (No Additional Interface Required) for Web Page Configuration
- Power Over Ethernet or External 24-48 V dc Supply
- SIP Compatible
- RJ45 LAN or WAN Direct Connection
- Four Contact Inputs and Two Relay Outputs
- Real-time Email Fault Reporting
- Surface-mount
- Full Keypad
- Hearing Aid Compatible
- Conformal-coated PCBA
- Non-moveable Hookswitch
- Handset with Noise-canceling Microphone and Hytrel® Coiled Cord (6-ft extended)
- Volume Control Pushbutton (Front Panel)
- NEMA 3R Weatherproof Rating
- FCC & IC Certified, UL60950 Listed
- Compatible with TMA (Telephone Management Application) Software

## General

Application	Indoor Use
Color	Gray
Connectivity Options	VoIP
Mount location	Surface-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55°C
Output Level Ringer	90 dBA @ 2 ft.
Signal Type	VoIP - SIP
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	Keypad
Weather Rating	Indoor

## Dimensions

Dimensions	6.9 in x 8 in x 9.5 in
Height	9.5 in
Length	6.9 in
Weight	4.8 lb
Width	8 in

## Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

## Certifications And Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15

## Product Assets

[Brochures - Rugged Telephone Brochure](#)  
[Configuration Guide - VoIP Telephone Configuration Guide: Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)  
[Configuration Guide - VoIP Telephone Basic Configuration Guide](#)  
[Installation Manuals - Rugged VoIP Handset Telephones](#)  
[Installation Manuals - VoIP - Software Configuration](#)  
[Literature - VoIP Handset Rugged Telephones](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
GTC-246710-SPEC-EN | REV 6/2024