



Behavioral Health Surface-Mount VoIP Telephone (Keypad)

By GAI-Tronics
Catalog # [210-710BH](#)

GAI-Tronics Behavioral Health series of rugged telephones are designed for use in environments where conversation privacy is desired but safety is a concern. The Model 210-710BH Surface-mount Handset Telephone is equipped with a shortened, 12-inch handset cord to prevent the handset being used as a weapon. The cord is also short enough to prevent the possibility of strangulation. Its rugged design provides both quality and longevity. The Model 210-700BH is a SIP-compatible telephone that is ideally suited for installation in any area requiring the Americans with Disabilities Act maximum protrusion Depth of 4 inches (corridors, hallways, passageways) or on any flat surface. The unit's rear mounting plate provides telephone line access, eliminating visibility of, or access to, cabling. Additionally, the 210-700BH is secured with security hardware to prevent vandalism.

Features

- Surface-Mount design for Indoor Use
- VoIP
- Braille Chrome-plated Keypad
- Brushed Stainless Steel Housing
- Front Panel Pushbutton Volume Control
- Handset with Noise-cancelling Microphone, Hearing Aid-compatible Receiver, and 12-inch Armored Cord with Anchored Lanyard

Application

- Rehabilitation Centers
- Correctional Facilities
- Mental Health Facilities

General

Catalog Number	210-710BH
Color	Silver
Connectivity Options	VoIP
Material	Front Panel: 14-gauge (0.075 inch) type 304 brushed stainless steel; Braille Dial Pad: Chrome-plated zinc
Mount location	Surface-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55 °C
Signal Type	VoIP - SIP
Specifications	UL/CSA, FCC
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)



Type	Keypad
Weather Rating	Indoor
Dimensions	
Cubic Capacity	58.81095 cu.in
Depth	3.27 in
Dimensions	10.0 in x 5.5 in x 3.27 in
Dimensions - Shipping	13.0 x 12.0 x 8.0
Height	3.27 in
Length	10 in
Weight	5.5 lb
Width	5.5 in

Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

Certifications And Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15

Product Assets

- [Brochures - Behavioral Health Telephones](#)
- [Brochures - Rugged Telephone Brochure](#)
- [Configuration Guide - VoIP Telephone Basic Configuration Guide](#)
- [Configuration Guide - VoIP Telephone Configuration Guide:](#)
- [Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
- [Literature - Behavioral Health Surface-mount VoIP Telephones](#)



A Hubbell brand