

121 Industrial Cable Gland

By Hawke
Catalog # 121



The 121 industrial cable gland is intended for use with non-armoured elastomer and plastic insulated cables in indoor and outdoor applications. This cable gland may be used with braided cables where the braid and outer sheath pass into the enclosure.

Features

- Metallic body construction
- Single elastomeric compression IP/retention seal on cable outer sheath
- Rounded cable entry to prevent cable damage
- Available with metric or NPT entry threadforms

Application

Industrial Applications

General

Catalog Number	121
Ingress Protection	IP66 and IP67 to IEC/EN 60529Deluge Protection to DTS01
Material	Manufactured in Brass, Nickel Plated Brass or 316L Stainless Steel
Operating Temperature	-60°C to +100 °C
Series	Industrial Cable Glands

Certifications And Compliance

Certification	• Ingress Protection: IP66 and IP67 to IEC/EN 60529 • Enclosure Protection: IK10 to IEC 62262 • Deluge Protection: to DTS01 • Construction & Test Standards: IEC/EN 62444 (Anchorage Type B)
Industry Standard(s)	IEC/EN 62444 (Anchorage Type B)
Non Hazardous Location	BS EN 62444:2013, BS 6121: Part 1 Type A2
Ratings	IK10 to IEC 62262

Product Assets

- 3D Models - 121 F 3" NPT
- 3D Models - 121 F 2-1/2 NPT
- 3D Models - 121 C2 1-1/4" NPT
- 3D Models - 121 E 2 NPT
- 3D Models - 121 C2 1-1/2 NPT
- 3D Models - 121 E 2-1/2" NPT
- 3D Models - 121 C 1" NPT
- 3D Models - 121 D 2" NPT
- 3D Models - 121 C 1-1/4" NPT
- 3D Models - 121 D 1-1/2" NPT
- 3D Models - 121 B 3/4" NPT
- 3D Models - 121 B 1" NPT
- 3D Models - 121 E M63 Metric
- 3D Models - 121 A 3/4" NPT
- 3D Models - 121 D M50 Metric
- 3D Models - 121 A 1/2" NPT
- 3D Models - 121 C2 M40 Metric
- 3D Models - 121 O M20 Metric
- 3D Models - 121 C M32 Metric
- 3D Models - 121 F M75 Metric
- 3D Models - 121 B M25 Metric
- 3D Models - 121 O 3/4" NPT
- 3D Models - 121 A M20 Metric
- 3D Models - 121 O 1/2" NPT
- Catalogs - Cable Glands Part Code Logic
- Certifications - ABS: 20-LD1964652-PDA
- Installation Manuals - AI464 (Maintaining IPx8 on Hawke Cable Glands)
- Installation Manuals - AI392 | Industrial Glands 121 Installation Instructions
- Literature - Maintaining Ingress Protection
- Specifications - Datasheet | 121
- Specifications - 121 Specification Sheet
- Specifications - 121 Specification Sheet French