



# B7021 - B7 Series, Combination Motor Starter, NEMA Size 0/1

By Killark  
Catalog # B7021

B7 Series-Combination Motor Starter- NEMA Size 0/1

## Features

- Type 4, 4X rated – providing protection from hose directed water and corrosion.
- Universal mounting pan, pre-drilled to facilitate easy field installation of starters.
- Provision for grounding supplied as standard.
- More wiring room meets latest NEC wire bend requirements.
- Quick release, captivated, 316 grade stainless steel cover bolts.
- Flange sealing gasket located to the inside of cover bolt to prevent water seepage into enclosure through bolt holes.
- Hinged cover provided as standard for an extra measure of safety and convenience.
- Breaker (MCP) handle can be padlocked in “ON” or “OFF” position.
- Provisions provided for drain and breather plus conduit openings for power and control.
- Reset button provided as standard.
- Two control operator openings provided plugged as standard.
- Additional openings can be factory or field drilled.
- Copper-free (less than 4/10 of 1% copper) enclosure.
- Bolt on bi-directional ductile mounting lugs.

## General

Catalog Number	B7021
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	30
Material	Copper-free aluminum
Series	B7
Size	1
UPC	783936020044



\*Representative Image

## Dimensions

Dimensions	4.5 in x 1 in x 6.5 in
Gross Weight with Packaging	78
Height	6.5 in
Length	4.5 in
Width	1 in

## Electrical Ratings

Voltage Rating	600 V
----------------	-------

## Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups B, C, D</li><li>• Class I, Zones 1 &amp; 2, Groups IIB+H2, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul>
Nema Rating	3, 4, 4X
UL File Number	E83696

## Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - B7 Series Enclosure UL Certifications](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL\\_B7021 Series Mounting Pan IOM\\_K1057](#)
- [Specifications - B7 Magnetic & Combination Motor Starters Specification Sheet](#)
- [Specifications - B7021 Specification Sheet French](#)
- [Specifications - B7021 Specification Sheet English](#)



A Hubbell brand