



EZ3S - EZ Series Vertical Conduit Seal-off with Preinstalled Dam Solution

By Killark
Catalog # [EZ3S](#)

Killark's EZ Seal offers the fastest and safest way to pour a seal fitting for hazardous classified electrical conduit systems. Its revolutionary and unconventional design offers virtually zero preparation prior to pouring the seal. The EZ Seal is the only seal-off on the market that allows the installer 360 degrees of unimpeded access to the conductors with minimal packing fiber required to dam the seal due to a preinstalled solution. No more tooling or frustrating attempts to separate the wires during the prepping process due to little spacing. Use everyone's favorite two-part epoxy resin, CELOX™ as the compound solution for fastest results.



Features

- Symmetrical and uniform design allows for a quicker installation due to immediate connection to the conduit - no more lining up pouring spouts
- Minimal turn radius offering optimized spacing for both enclosures and conduit
- 360° unimpeded access to potting chamber allowing simplified compound pouring
- Pre-installed disc brush damming technology to drastically reduce packing fiber and installation time
- Retrofittable in case the need to rerun wires occur
- Certified to both fast curing two-part epoxy resin, CELOX, and the traditional SC sealing compound
- Type 3R rated for outdoor applications

Application

Class I, Divisions 1 and 2: The purpose of seals in a Class I hazardous location is to minimize the passage of gases and vapors and prevent the passage of flames from one electrical installation to another through the conduit system

General

Finish Type	Natural
Material	Zinc Plated Steel
Series	EZ Series
UPC	783936185521

Dimensions

Height	5.081 in
Hub Size	1"
Weight	1.77 lb
Width	1.961 in

Certifications and Compliance

Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups A, B, C, DClass II, Divisions 1 & 2, Groups E, F, GClass III, Divisions 1 & 2
Nema Rating	3R
UL File Number	E10514

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [3D Models - EZ3 & EZ3S Open 3D Model \(STP\)](#)
- [3D Models - EZ3 & EZ3S 3D Model \(STP\)](#)
- [Brochures - EZ Seal Next Generation of Hazardous-Rated Seal Fittings](#)
- [Catalog Page - EZ Series The Next Generation of Vertical Seal Fittings](#)
- [Certifications - EZ Seal Series UL Certificate of Compliance](#)
- [Engineering Drawing - EZ3 & EZ3S Engineering Drawing \(DWG\)](#)
- [Installation Manuals - EZ Seal Retro Fit IOM](#)
- [Installation Manuals - EZ Seal IOM](#)
- [Sales Drawings - EZ2 & EZ2S Sales Drawing \(PDF\)](#)
- [Video](#)

Related Products

- [KQS-250 ML - KQS-250 ML - CELOX™ 250ml Killark Quick Sealing Compound With Four Static Mixing Nozzles](#)
- [KQS-250 GUN - KQS-250 GUN - CELOX™ 250ml Killark Quick Sealing Compound Dispensing Gun](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
KILL-EZ3S-SPEC-EN | REV 7/2023

