



VML-X Series LED Area light 75 Watt, 120-277VAC, 9000 Lumen 1" Wall Bracket

By Killark
Catalog # [VML1X930B3G](#)



The VML-X Series is an Area Light fixture using energy efficient LED's. The redesigned CertiLite VML-X uses optics on the LED's to direct the light to where it is needed. This fixture is made with a cast copper-free aluminum housing and mount that is suitable for harsh and hazardous environments. The design of this fixture internal heat sink keeps a clean look on the outside of the fixture creating a LED fixture that does not contain external heat fins. Easily Retro fit any old HID or LED fixture to the new VML-X for a cleaner more efficient light.

Features

Wildlife Friendly Color options

General

Application	Class I Division 2 Hazardous Locations Class II Hazardous Dust Zone 2 Hazardous Locations Off and On Shore Oil and Gas Wet and Marine Locations Food and Beverage Heavy Industrial
Catalog Number	VML1X930B3G
Color Temperature	5000 K
Finish Type	Powder Epoxy Paint
Light Source	LED
Lumen Range	5,000 - 9,000 lm
Lumens	9000
Mounting Type	Wall Bracket
Optic Type	Glass Globe
Series	VML-X

Dimensions

Hub Size	1"
----------	----

Electrical Ratings

Current / Amperage Rating	0.63-0.27 A
Frequency Rating	50-60 Hz
Voltage Rating	120-277 VAC
Wattage	75 W

Certifications And Compliance

Hazardous Rating(s)	Class I, Div2, Groups A,B,C,D Class I, Zone 2, Groups IIC, IIB, IIA Class II, Div. 1&2, Groups E,F,G IECEX QPS 15.0006 Ex ec IIC T4/T3 Gc Ex tb IIIC T4/T3 Db QPS 22ATEX7000
---------------------	--

Product Assets

- [Brochures - VML-X Series for Harsh and Hazardous Environments](#)
- [Brochures - VML-X Series Hazardous Location Luminaires Brochure](#)
- [Catalog Page - VML-X Series Catalog Pages](#)
- [Catalogs - Killark Catalog](#)
- [Certifications - VMLX/VM4L Series EU Type ATEX Certificate](#)
- [Certifications - VMLX & VM4L Series Attestation of Conformity](#)
- [Certifications - VMLX & VM4L Series IECEx Certification](#)
- [Certifications - VMLX/VM4L Series ATEX Certificate](#)
- [Certifications - VMLX Series QPS North American Certification](#)
- [Installation Manuals - VMLX Series IOM K1531](#)
- [Photometry - KIL_VML1X930N](#)
- [Photometry - KIL_VML1X930NAR](#)
- [Photometry - KIL_VML1X930NDR](#)
- [Video - VML-X Features and Benefits](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL-VML1X930B3G-SPEC-EN | REV 6/2024